



## Reversing bridge, for DILM7-M12

**Part no.** DILM12-XR  
**Catalog No.** 110099  
**Alternate Catalog No.** XTCEXRBB-OA2  
**EL-Nummer (Norway)** 0004361008

## Delivery program

|                |  |  |                                                                                                              |
|----------------|--|--|--------------------------------------------------------------------------------------------------------------|
| Basic function |  |  | Connection system SmartWire                                                                                  |
| Description    |  |  | To assemble reversing starters with tool-less plug connection for use with DILM7 - DILM15, without A2 bridge |

## Technical data

## General

|                     |  |  |           |
|---------------------|--|--|-----------|
| Ambient temperature |  |  | -25 - +60 |
|---------------------|--|--|-----------|

## Main conducting paths

|                                       |           |      |           |
|---------------------------------------|-----------|------|-----------|
| Rated impulse withstand voltage       | $U_{imp}$ | V AC | 6000      |
| Overvoltage category/pollution degree |           |      | III/3     |
| Rated operational voltage             | $U_e$     | V    | 230 - 415 |
| Rated operational current             |           |      |           |
| Open, 3-pole: 50 – 60 Hz              |           |      |           |
| 380 V 400 V                           | $I_e$     | A    | 12        |

## Additional technical data

|                                             |  |  |                                                                                                                                                                                                                                           |
|---------------------------------------------|--|--|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Motor protective circuit breaker PKZM0, PKE |  |  | PKZM0 motor-protective circuit-breakers, see motor-protective circuit-breakers/<br>PKZM0 product group<br>DILM contactors, see contactor product group<br>DILET timing relay, ETR, see contactors, electronic timing relays product group |
|---------------------------------------------|--|--|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

## Design verification as per IEC/EN 61439

|                                                                                                                        |            |    |                                                                    |
|------------------------------------------------------------------------------------------------------------------------|------------|----|--------------------------------------------------------------------|
| Technical data for design verification                                                                                 |            |    |                                                                    |
| Rated operational current for specified heat dissipation                                                               | $I_n$      | A  | 22                                                                 |
| Heat dissipation per pole, current-dependent                                                                           | $P_{vid}$  | W  | 0.7                                                                |
| Equipment heat dissipation, current-dependent                                                                          | $P_{vid}$  | W  | 2.1                                                                |
| Static heat dissipation, non-current-dependent                                                                         | $P_{vs}$   | W  | 0                                                                  |
| Heat dissipation capacity                                                                                              | $P_{diss}$ | W  | 0                                                                  |
| Operating ambient temperature min.                                                                                     |            | °C | -25                                                                |
| Operating ambient temperature max.                                                                                     |            | °C | 60                                                                 |
| IEC/EN 61439 design verification                                                                                       |            |    |                                                                    |
| 10.2 Strength of materials and parts                                                                                   |            |    |                                                                    |
| 10.2.2 Corrosion resistance                                                                                            |            |    | Meets the product standard's requirements.                         |
| 10.2.3.1 Verification of thermal stability of enclosures                                                               |            |    | Meets the product standard's requirements.                         |
| 10.2.3.2 Verification of resistance of insulating materials to normal heat                                             |            |    | Meets the product standard's requirements.                         |
| 10.2.3.3 Verification of resistance of insulating materials to abnormal heat and fire due to internal electric effects |            |    | Meets the product standard's requirements.                         |
| 10.2.4 Resistance to ultra-violet (UV) radiation                                                                       |            |    | Meets the product standard's requirements.                         |
| 10.2.5 Lifting                                                                                                         |            |    | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.2.6 Mechanical impact                                                                                               |            |    | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.2.7 Inscriptions                                                                                                    |            |    | Meets the product standard's requirements.                         |
| 10.3 Degree of protection of ASSEMBLIES                                                                                |            |    | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.4 Clearances and creepage distances                                                                                 |            |    | Meets the product standard's requirements.                         |
| 10.5 Protection against electric shock                                                                                 |            |    | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.6 Incorporation of switching devices and components                                                                 |            |    | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.7 Internal electrical circuits and connections                                                                      |            |    | Is the panel builder's responsibility.                             |
| 10.8 Connections for external conductors                                                                               |            |    | Is the panel builder's responsibility.                             |
| 10.9 Insulation properties                                                                                             |            |    |                                                                    |

|                                                          |  |                                                                                                                                  |
|----------------------------------------------------------|--|----------------------------------------------------------------------------------------------------------------------------------|
| 10.9.2 Power-frequency electric strength                 |  | Is the panel builder's responsibility.                                                                                           |
| 10.9.3 Impulse withstand voltage                         |  | Is the panel builder's responsibility.                                                                                           |
| 10.9.4 Testing of enclosures made of insulating material |  | Is the panel builder's responsibility.                                                                                           |
| 10.10 Temperature rise                                   |  | The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices. |
| 10.11 Short-circuit rating                               |  | Is the panel builder's responsibility. The specifications for the switchgear must be observed.                                   |
| 10.12 Electromagnetic compatibility                      |  | Is the panel builder's responsibility. The specifications for the switchgear must be observed.                                   |
| 10.13 Mechanical function                                |  | The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.                         |

## Technical data ETIM 7.0

|                                                                                                                                                                                                                                                   |  |                   |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|-------------------|
| Low-voltage industrial components (EG000017) / Accessories for low-voltage switch technology (EC002498)                                                                                                                                           |  |                   |
| Electric engineering, automation, process control engineering / Low-voltage switch technology / Component for low-voltage switching technology / Component for low-voltage switch technology (accessories) (ecl@ss10.0.1-27-37-13-92 [AKN570013]) |  |                   |
| Type of accessory                                                                                                                                                                                                                                 |  | Connecting bridge |

## Approvals

|                                      |  |                                                           |
|--------------------------------------|--|-----------------------------------------------------------|
| Product Standards                    |  | IEC/EN 60947-4-1; UL 508; CSA-C22.2 No. 14-05; CE marking |
| UL File No.                          |  | E36332                                                    |
| UL Category Control No.              |  | NLRV                                                      |
| CSA File No.                         |  | 012528                                                    |
| CSA Class No.                        |  | 3211-05                                                   |
| North America Certification          |  | UL listed, CSA certified                                  |
| Specially designed for North America |  | No                                                        |