




Test probes

PRUEF 2 S



4 mm sliding sleeve system

Product	PRUEF 2 S
description	Contact-protected test probe with elastic, shatter-proof insulating sleeve and slender stainless steel tip. Tip penetrates insulation and oxide layers. Insulated brass 4 mm diameter socket connection. Connects with sliding sleeve measuring leads. Accessory tip protector and IC tap SS 260.
article-no. / *colour	9736591xx <div style="display: flex; justify-content: space-around; align-items: center;"> <div style="text-align: center;">  00 black </div> <div style="text-align: center;">  01 red </div> </div>
drawing	
technical data	
connection	unsprung socket 4 mm
rated voltage ⁽¹⁾	30 VAC / 60 VDC
measurement cat. acc. to IEC 61010	O ⁽³⁾
material socket	brass
housing material	PP / TPE
temperature range acc. To IEC61010 ⁽²⁾	-25 °C to +80 °C
inflammability class acc. to UL 94 (only valid for basic material of housing)	HB
standard	IEC 61010

⁽¹⁾ for normal environmental conditions -5°C to +40°C

⁽²⁾ contact the manufacturer for applications at deviating temperature ranges

⁽³⁾ without rated measurement category, for other circuits that are not directly connected to mains

stand: 09.07.2018