

Data Sheet

750pcs 2:1 Heat Shrink Tube Assortment

Typ. T1905CA055

This range is particularly suitable for hobbyists, craftsmen, field service, service workshops, electronics and the laboratory needs.

750 pieces of shrinking ration 2:1 standard shrinking tube for a range of application diameter from 1.5 to 12.0 mm.

The heat-shrink tubing can be used for insulation, protective covering of components, as anti-kink protection, protection against corrosion, as well as repair of cables and lines, and much more be used.





Material: Polyethylene(PE)

Shrinking ratio: 2:1

Operating Temperature: -40 ~110°C

Minimum shrink temperature: 70°C

Full recovery temperature: 110°C



Section	Heat shrink tube		Length	pcs
	Inner diameter \varnothing	after shrink \varnothing		
1,2	1.5 mm	0.85 mm	45 mm	125
3,4	2.5 mm	1.3 mm	45 mm	110
5	3.5 mm	1.8 mm	65 mm	60
6	5.0 mm	2.5 mm	65 mm	30
7	6.0 mm	3.0 mm	45 mm	25
8	8.0 mm	4.0 mm	45 mm	55
9	9.0 mm	4.5 mm	65 mm	55
10	12.0 mm	6.0 mm	65 mm	55