




Dept Qty  
DC 1  
ED 1  
IE 1  
ISO 1  
PD 1  
R&D 1  
SD 1  
QA 1  
QC 1  
QE 1

The information provided herein is from CONNLY Electronic Co., Ltd. and is confidential. Any disclosure to a party other than the recipient is prohibited. The intellectual properties and its rights contained herein, including but not limited to, trademarks, patents, copyrights, trade secrets, and technical know-how, are owned exclusively by CONNLY or its affiliates. Unauthorized use or reproduction of this document in any form or by any means, electronic or mechanical, including photocopying, recording, or by any information storage and retrieval system, without the prior written permission of CONNLY is strictly prohibited. CONNLY may enforce its intellectual property rights at its own discretion, failures or delays to exercise such rights does not constitute a waiver of such rights.

# U TYPE



N: NUMBER OF CONTACTS



RECOMMEND P.C.BOARD LAYOUT

TABLE A:

| TYPE | Dimension |       |      | Pin Length<br>(mm) |
|------|-----------|-------|------|--------------------|
|      | A         | B     | C    |                    |
| 1    | 3.00      | 6.00  | 6.07 | 15.50              |
| 2    | 4.00      | 6.90  | 3.40 | 14.70              |
| 3    | 6.00      | 11.40 | 5.64 | 23.40              |
| 4    | 3.75      | 3.40  | 3.40 | 11.00              |
| 5    | 2.80      | 4.00  | 3.40 | 10.60              |
| 6    | 5.85      | 7.90  | 3.40 | 17.50              |
| 7    | 3.60      | 3.20  | 3.40 | 10.60              |
| 8    | 6.30      | 3.20  | 4.36 | 14.20              |
| 9    | 3.00      | 6.00  | 5.42 | 15.00              |
| 10   | 3.64      | 5.76  | 6.48 | 16.30              |
| 11   | 3.00      | 6.00  | 5.00 | 14.40              |
| 12   | 3.10      | 3.40  | 3.40 | 10.50              |
| 13   | 6.00      | 4.90  | 3.40 | 14.70              |
| 14   | 6.30      | 3.00  | 3.40 | 13.10              |
| 15   | 6.20      | 3.70  | 3.60 | 14.00              |
| 16   | 3.00      | 6.30  | 4.20 | 14.00              |
| 17   | 2.30      | 5.11  | 5.30 | 13.10              |
| 18   | 6.20      | 3.80  | 3.40 | 13.80              |
| 19   | 4.70      | 4.70  | 4.20 | 14.00              |
| 20   | 4.00      | 6.93  | 5.50 | 16.85              |
| 21   | 2.50      | 5.40  | 4.50 | 12.80              |
| 22   | 5.10      | 3.50  | 4.00 | 13.10              |
| 23   | 3.00      | 4.40  | 4.00 | 11.85              |
| 24   | 3.00      | 4.75  | 4.00 | 12.15              |
| 25   | 4.70      | 4.80  | 3.70 | 13.70              |
| 26   | 3.00      | 12.50 | 5.00 | 20.95              |
| 27   | 5.80      | 4.30  | 3.34 | 13.85              |
| 28   | 2.50      | 5.20  | 4.30 | 12.40              |
| 29   | 3.00      | 6.20  | 6.45 | 16.10              |
| 30   | 3.00      | 6.00  | 4.30 | 13.80              |
| 31   | 7.50      | 7.80  | 4.00 | 19.80              |
| 32   | 3.00      | 7.00  | 6.07 | 16.50              |
| 33   | 3.00      | 6.00  | 6.57 | 16.00              |
| 34   | 6.00      | 4.40  | 3.68 | 14.50              |
| 35   | 3.07      | 5.92  | 6.50 | 15.90              |
| 36   | 3.30      | 3.15  | 5.10 | 12.00              |
| 37   | 3.00      | 6.50  | 4.50 | 14.40              |
| 38   | 3.00      | 6.50  | 5.07 | 15.00              |
| 39   | 6.00      | 2.40  | 4.20 | 13.00              |
| 40   | 6.10      | 3.20  | 4.36 | 14.10              |
| 41   | 4.20      | 4.20  | 4.20 | 13.00              |
| 42   | 2.60      | 11.00 | 8.20 | 22.20              |
| 43   | 3.00      | 6.00  | 4.00 | 13.40              |
| 44   | 5.72      | 5.10  | 4.26 | 15.50              |
| 45   | 3.00      | 3.00  | 4.00 | 10.50              |
| 46   | 3.00      | 5.80  | 6.50 | 15.80              |

A/B/C: CUSTOMER LENGTH AVAILABLE

| REV. | DESCRIPTION    | DRAWN         | CHECKED | APPROVED      |
|------|----------------|---------------|---------|---------------|
| A    | NEW RELEASE    | LJH 09/15/05' |         | LJC 09/15/05' |
| M    | DRAWING UPDATE | JLZ 12/17/18' |         |               |
|      |                |               |         |               |
|      |                |               |         |               |

## NOTES:

### SPECIFICATIONS:

- CONTACT RESISTANCE: 20mΩ MAX.
- INSULATION RESISTANCE: 1000MΩ MIN.
- DIELECTRIC WITHSTANDING VOLTAGE: 600V AC(RMS) FOR 1 MINUTE.
- CURRENT RATING: 3A.
- VOLTAGE RATING: 250V AC RMS.
- TEMPERATURE: -40°C~+105°C.

### MATERIALS:

- CONTACT MATERIAL: COPPER ALLOY.
- CONTACT PLATING: GOLD PLATING OVER NICKEL.
- INSULATOR MATERIALS: PBT, BLACK, UL94-V0.

### PRODUCT NUMBER CODE:

DS1022- X X U X X - X

PLATING LEVEL(FOR GOLD ONLY)  
3A: LEVEL 3A B: LEVEL B  
N: LEVEL N

Dim. A B C type  
1: Type 1  
2: Type 2 .....  
or -A\*-\*B\*-\*C\*.\*

CONTACT PLATING  
F1: FULL GOLD FLASH  
6: FULL TIN

BEND TYPE  
U: U TYPE

MOUNTING TYPE  
R: R/A

No.OF CONTACTS  
1x1 - 1x40

|    |      |      |      |       |
|----|------|------|------|-------|
| 47 | 3.30 | 5.80 | 4.36 | 14.00 |
| 48 | 3.50 | 6.32 | 5.50 | 15.70 |
| 49 | 4.00 | 7.90 | 3.30 | 15.70 |
| 50 | 3.50 | 2.20 | 4.30 | 10.50 |
| 51 | 3.00 | 3.00 | 4.30 | 10.80 |
| 52 | 3.00 | 5.20 | 3.80 | 12.50 |

| GENERAL TOLERANCE |                      | ANGLE TOLERANCE |        |
|-------------------|----------------------|-----------------|--------|
| X.                | ±0.60                | X.              | ±5°    |
| .X                | ±0.38                | .X              | ±3°    |
| .XX               | ±0.25                | .XX             | ±2°    |
| DRAWING TYPE      |                      | CUSTOMER        |        |
| SCALE             | 1:1                  | SHEET           | 1 OF 5 |
| DRAWING NO.       | C-DS1022-1xXXUXX-X-M |                 |        |

| PROJECTION |    | TITLE                                           |
|------------|----|-------------------------------------------------|
| UNITS      | mm | 2.54mm PIN HEADER R/A TYPE<br>SINGLE ROW U TYPE |
| SHEET SIZE | A4 | SERIES DS1022 SERIES                            |




晨翔电子有限公司  
CONNFLY CONNLY ELECTRONIC CO. LTD


Dept  
Qty  
DC 1  
ED 1  
IE 1  
ISO 1  
PD 1  
R&D 1  
SD 1  
QA 1  
QC 1  
QE 1

The information provided herein is from CONNLY Electronic Co., Ltd. and is confidential. Any disclosure to a party other than the recipient is prohibited. The intellectual properties and its rights contained herein, including but not limited to, trademarks, patents, copyrights, trade secrets, and technical know-how, are owned exclusively by CONNLY or its affiliates. Unauthorized use or reproduction of this document in any form without the prior written permission of CONNLY is strictly prohibited. CONNLY may enforce its intellectual property rights at its own discretion, failures or delays to exercise such rights does not constitute a waiver of such rights.

# D TYPE



N: NUMBER OF CONTACTS



RECOMMEND P.C.BOARD LAYOUT

TABLE A:

| TYPE | Dimension |       |       | Pin Length (mm) |
|------|-----------|-------|-------|-----------------|
|      | A         | B     | C     |                 |
| 1    | 6.00      | 3.00  | 10.36 | 13.80           |
| 2    | 6.00      | 4.50  | 9.50  | 14.40           |
| 3    | 6.10      | 4.00  | 10.40 | 14.80           |
| 4    | 6.00      | 3.20  | 10.50 | 14.10           |
| 5    | 6.00      | 3.50  | 10.82 | 14.70           |
| 6    | 4.70      | 1.73  | 8.20  | 10.40           |
| 7    | 15.00     | 3.00  | 19.08 | 22.50           |
| 8    | 6.00      | 3.10  | 11.10 | 14.40           |
| 9    | 1.00      | 1.91  | 5.00  | 7.40            |
| 10   | 6.20      | 3.20  | 11.10 | 14.70           |
| 11   | 6.20      | 3.20  | 10.8  | 14.40           |
| 12   | 4.50      | 2.93  | 8.00  | 11.40           |
| 13   | 6.30      | 2.60  | 10.36 | 13.40           |
| 14   | 5.70      | 2.95  | 9.52  | 12.90           |
| 15   | 4.80      | 3.00  | 8.10  | 11.50           |
| 16   | 6.00      | 3.00  | 9.14  | 12.60           |
| 17   | 7.20      | 3.00  | 10.36 | 13.80           |
| 18   | 3.00      | 6.00  | 7.50  | 13.80           |
| 19   | 3.00      | 6.00  | 9.32  | 15.80           |
| 20   | 3.50      | 3.00  | 7.86  | 11.30           |
| 21   | 5.00      | 2.70  | 8.14  | 11.30           |
| 22   | 8.20      | 2.80  | 12.30 | 15.50           |
| 23   | 3.00      | 3.00  | 7.36  | 10.80           |
| 24   | 6.50      | 3.00  | 10.36 | 13.80           |
| 25   | 6.80      | 8.40  | 10.64 | 19.50           |
| 26   | 10.00     | 3.20  | 14.40 | 18.00           |
| 27   | 3.50      | 2.50  | 7.82  | 10.80           |
| 28   | 6.00      | 3.00  | 9.50  | 12.90           |
| 29   | 7.00      | 3.10  | 13.90 | 17.50           |
| 30   | 4.00      | 3.00  | 8.36  | 11.80           |
| 31   | 3.00      | 5.40  | 8.65  | 14.50           |
| 32   | 4.50      | 4.50  | 8.82  | 17.80           |
| 33   | 3.20      | 6.00  | 7.50  | 14.00           |
| 34   | 3.80      | 6.00  | 8.30  | 14.80           |
| 35   | 3.00      | 3.40  | 8.00  | 11.80           |
| 36   | 3.80      | 3.00  | 7.93  | 11.20           |
| 37   | 16.4      | 13.00 | 19.60 | 33.00           |
| 38   | 3.20      | 3.20  | 7.20  | 11.00           |
| 39   |           |       |       |                 |
| 40   |           |       |       |                 |
| 41   |           |       |       |                 |
| 42   |           |       |       |                 |

A/B/C: CUSTOMER LENGTH AVAILABLE

## NOTES:

### SPECIFICATIONS:

- CONTACT RESISTANCE: 20mΩ MAX.
- INSULATION RESISTANCE: 1000MΩ MIN.
- DIELECTRIC WITHSTANDING VOLTAGE: 600V AC(RMS) FOR 1 MINUTE.
- CURRENT RATING:3A.
- VOLTAGE RATING:250V AC RMS.
- TEMPERATURE: -40°C~+105°C.

### MATERIALS:

- CONTACT MATERIAL: COPPER ALLOY.
- CONTACT PLATING: GOLD PLATING OVER NICKEL.
- INSULATOR MATERIALS: PBT, BLACK, UL94-V0.

### PRODUCT NUMBER CODE:

DS1022- X X D X X - X

PLATING LEVEL(FOR GOLD ONLY)  
3A: LEVEL 3A B: LEVEL B  
N: LEVEL N

Dim. A B C type  
1: Type 1  
2: Type 2 .....  
or -A\*-B\*-C\*.\*

CONTACT PLATING  
F1: FULL GOLD FLASH  
6: FULL TIN

BEND TYPE  
D: D TYPE

MOUNTING TYPE  
R: R/A

No.OF CONTACTS  
1x1 - 1x40

| GENERAL TOLERANCE |       | ANGLE TOLERANCE      |       | PROJECTION |                                                                  | TITLE  | 2.54mm PIN HEADER R/A TYPE<br>SINGLE ROW D TYPE |  |
|-------------------|-------|----------------------|-------|------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|--------|-------------------------------------------------|--|
| X.                | ±0.60 | X.                   | ±5°   | UNITS      | mm                                                                                                                                                    |        |                                                 |  |
| .X                | ±0.38 | .X                   | ±3°   | SHEET SIZE | A4                                                                                                                                                    | SERIES | DS1022 SERIES                                   |  |
| .XX               | ±0.25 | .XX                  | ±2°   |            |                                                                                                                                                       |        |                                                 |  |
| DRAWING TYPE      |       | CUSTOMER             |       |            | <div><p>晨翔电子有限公司<br/>CONNFLY CONNLY ELECTRONIC CO. LTD</p></div> |        |                                                 |  |
| SCALE             |       | 1:1                  | SHEET | 2 OF 5     |                                                                                                                                                       |        |                                                 |  |
| DRAWING NO.       |       | C-DS1022-1xXXDXX-X-L |       |            |                                                                                                                                                       |        |                                                 |  |

|   | Dept | Qty |
|---|------|-----|
| A | DC   | 1   |
|   | ED   | 1   |
|   | IE   | 1   |
|   | ISO  | 1   |
| B | PD   | 1   |
|   | R&D  | 1   |
|   | SD   | 1   |
|   | QA   | 1   |
| C | QC   | 1   |
|   | QE   | 1   |
| D |      |     |
| E |      |     |
| F |      |     |
| G |      |     |
| H |      |     |

| REV. | DESCRIPTION    | DRAWN         | CHECKED                                                                           | APPROVED      |
|------|----------------|---------------|-----------------------------------------------------------------------------------|---------------|
| A    | NEW RELEASE    | LJH 09/15/05' |  | LJC 09/15/05' |
| L    | DRAWING UPDATE | JLZ 12/17/18' |  |               |
|      |                |               |                                                                                   |               |
|      |                |               |                                                                                   |               |

NOTES:

**SPECIFICATIONS:**

1. CONTACT RESISTANCE: 20mΩ MAX.
2. INSULATION RESISTANCE: 1000MΩ MIN.
3. DIELECTRIC WITHSTANDING VOLTAGE: 600V AC(RMS) FOR 1 MINUTE.
4. CURRENT RATING:3A.
5. VOLTAGE RATING:250V AC RMS.
6. TEMPERATURE: -40°C~+105°C.

**MATERIALS:**

1. CONTACT MATERIAL: COPPER ALLOY.
2. CONTACT PLATING: GOLD PLATING OVER NICKEL.
3. INSULATOR MATERIALS: PBT,BLACK,UL94-V0.

PRODUCT NUMBER CODE:

DS1022- X X X X - X

PLATING LEVEL(FOR GOLD ONLY)  
3A: LEVEL 3A    B: LEVEL B  
N: LEVEL N

- Dim. A B C type
- 1: Type 1
- 2: Type 2 .....
- or -A\*.\*-B\*.\*-C\*.\*



CONTACT PLATING  
F1: FULL GOLD FLASH  
6: FULL TIN

MOUNTING TYPE  
R: R/A

No.OF CONTACTS  
2x1 - 2x40

RIGHT ANGLE  
TABLE A:

| TYPE | Dimension |      |       | Pin Length<br>(mm) |
|------|-----------|------|-------|--------------------|
|      | A         | B    | C     |                    |
| 1    | 6.00      | 3.00 | 13.04 | 14.00<br>19.00     |
| 2    | 6.10      | 4.00 | 12.94 | 15.00<br>20.00     |
| 3    | 6.00      | 4.00 | 12.76 | 14.80<br>19.80     |
| 4    | 9.00      | 3.00 | 16.04 | 17.00<br>22.00     |
| 5    | 6.00      | 3.00 | 13.80 | 14.80<br>19.80     |
| 6    | 5.10      | 3.00 | 13.04 | 14.00<br>19.00     |
| 7    | 6.50      | 3.00 | 13.10 | 14.00<br>19.00     |
| 8    | 3.00      | 6.00 | 9.32  | 18.30<br>13.20     |
| 9    | 3.00      | 3.00 | 10.90 | 11.80<br>16.80     |
| 10   | 7.00      | 3.10 | 13.90 | 15.00<br>20.00     |
| 11   | 4.00      | 3.00 | 10.76 | 11.80<br>16.80     |



RECOMMEND PCB LAYOUT  
(TOLERANCE  $\pm 0.05$ )

|                   |                    |                 |        |                                                                                                                                                    |                                                                                       |            |                            |
|-------------------|--------------------|-----------------|--------|----------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|------------|----------------------------|
| GENERAL TOLERANCE |                    | ANGLE TOLERANCE |        | PROJECTION                                                                                                                                         |  | TITLE      | 2.54mm PIN HEADER R/A TYPE |
| X. ±0.60          | X. ±5°             |                 |        | UNITS                                                                                                                                              | mm                                                                                    | DOUBLE ROW |                            |
| .X ±0.38          | .X ±3°             |                 |        | SHEET SIZE                                                                                                                                         | A4                                                                                    | SERIES     | DS1022 SERIES              |
| .XX ±0.25         | .XX ±2°            |                 |        |  <b>晨翔电子有限公司</b><br><b>CONNFLY CONNFLY ELECTRONIC CO. LTD</b> |                                                                                       |            |                            |
| DRAWING TYPE      | CUSTOMER           |                 |        |                                                                                                                                                    |                                                                                       |            |                            |
| SCALE             | 1:1                | SHEET           | 3 OF 5 |                                                                                                                                                    |                                                                                       |            |                            |
| DRAWING NO.       | C-DS1022-2xXXX-X-L |                 |        |                                                                                                                                                    |                                                                                       |            |                            |



The information provided herein is from CONNELLY Electronic Co., Ltd., and is confidential. Any disclosure to a party other than the recipient is prohibited. The intellectual properties and its rights contained herein, including but not limited to, trademarks, patents, copyrights, trade secrets, and technical know-how, are owned exclusively by CONNELLY or its affiliates. Unauthorized use or modification is strictly prohibited without prior written consent from CONNELLY. All intellectual properties provided herein are for reference purposes only and does not constitute authorization of its use in any format or manner. CONNELLY may enforce its intellectual property rights at its own discretion; failures or delays to exercise such rights does not constitute a waiver of such rights.

PLATING LEVEL(FOR GOLD ONLY)  
3A: LEVEL 3A B: LEVEL B

PACKING TYPE  
T: TRAY  
R: TAPE ON REEL  
B: TUBE

PICK UP SUPPORT  
S: W/ PICK UP  
X: W/O PICK UP


Dim. A B C type  
1: Type 1.....  
or -A\*.\*-B\*.\*-C\*.\*

CONTACT PLATING  
F1: FULL GOLD FLASH  
6: FULL TIN

BEND TYPE (SINGLE ROW ONLY)  
A: R1 TYPE  
B: R2 TYPE

MOUNTING TYPE  
M: SMT

No.OF CONTACTS  
1x2 - 1x40  
2x2 - 2x40



The image contains two technical drawings of ball bearings. The left drawing is labeled 'DOUBLE ROW' and shows a cross-section of a double-row bearing. It has an outer diameter of 7.00, an inner diameter of 2.54, a width of 4.00, and a bore diameter of  $B \pm 0.25$ . The right drawing is labeled 'SINGLE ROW' and shows a cross-section of a single-row bearing. It has an outer diameter of 7.00, a width of 5.00, and a bore diameter of  $B \pm 0.25$ . Both drawings show the balls and the cage, with dimensions for the outer ring, inner ring, and balls.

| pos. \ Dim. | Dim.D |
|-------------|-------|
| 2~4pin      | 5.0mm |
| 5~40pin     | 8.0mm |
| Single Row  | 7.0mm |

|            |                                                                                       |                                  |               |
|------------|---------------------------------------------------------------------------------------|----------------------------------|---------------|
| PROJECTION |  | TITLE                            |               |
| UNITS      | mm                                                                                    | PIN HEADER PITCH 2.54mm SMT TYPE |               |
| SHEET SIZE | A4                                                                                    | SERIES                           | DS1022 SERIES |

