

Wireless module - FL WLAN 1100 - 2702534

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



WLAN access point, client with two internal antennas (MIMO) for single-hole mounting, IP54, WLAN 802.11 a, b, g, n, frequency: 2.4 GHz, 5 GHz (incl. DFS channels), connections: COMBICON 9 ... 32 V DC, RJ45: for LAN, web, http/https, Command Line Interface

WLAN

Key commercial data

package_quantity	1
GTIN	4055626278919

Technical data

Dimensions

Width	62.8 mm
Height	36.5 mm
Depth	113.2 mm
Note on dimensions	Outside dimensions

Ambient conditions

Ambient temperature (operation)	0 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)
Air pressure (operation)	800 hPa ... 1080 hPa (up to 2000 m above sea level)
Air pressure (storage/transport)	660 hPa ... 1080 hPa (up to 3500 m above sea level)
Degree of protection	IP54
Note	Degree of protection when installed

Wireless interface

Designation	Wireless LAN
Wireless standard	IEEE 802.11
	a
	b
	g
	n
Antenna connection method	(Internal)
Frequency band	2.4 GHz
	5 GHz

Wireless module - FL WLAN 1100 - 2702534

Technical data

Wireless interface

Transmission power	max. 20 dBm (EIRP)
Number of wireless interfaces	1 IEEE 802. 11 a/b/g/n
Wireless modules that can be connected	10 (In Access Point mode max. 2 SSIDs)

Functions

Operating modes	Access Point / Client Adapter / Repeater
Configuration	Web-based management, automated CLI
Quality of service (QoS)	Yes
Security	802.11i
	WPA PSK (preshared key)
	WPA2
	AES
	TKIP
	MAC filter

Wireless card

Number	1
Type	IEEE 802.11 a/b/g/n 2.4 GHz and 5 GHz to 300 Mbps
Assembly instructions	Permanently installed

Antenna

Assembly instructions	Internal antenna
Number	2
Connection method	permanently installed
Note on the connection method	MIMO
Gain	5 dBi

Ethernet interface

Interface	Ethernet (RJ45)
Number of interfaces	1
Connection method	RJ45
Note on the connection method	Auto negotiation and autocrossing
Transmission speed	10/100 Mbps
Transmission physics	Copper
Transmission length	100 m (per segment)

Power supply for module electronics

Connection technology	COMBICON
Connection method	Push-in spring connection
Designation	1966101 FMC 1,5/ 3-STF-3,5
Number of positions	3
Cross section range AWG	24 ... 16 (Use copper wires rated 75° C (UL))
Note on the connection method	Recommended conductor cross section: 0.75 mm ²
	Recommended ferrule: connection length 10 mm

Wireless module - FL WLAN 1100 - 2702534

Technical data

Power supply for module electronics

	Recommended crimping pliers: trapezoidal or square
Supply voltage	24 V DC (SELV)
Supply voltage range	18 V DC ... 32 V DC (PELV/SELV)
	9 V DC ... 32 V DC (PELV/SELV (as of HW version 05))
Supply current	typ. 120 mA (at 24 V DC)
Current consumption	max. 250 mA (at 18 V DC)
	max. 400 mA (at 9 V DC)

Connection data

Designation	1966101 FMC 1,5/ 3-STF-3,5
Connection method	Push-in spring connection
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	1.5 mm ²
Conductor cross section flexible min.	0.2 mm ²
Conductor cross section flexible max.	1.5 mm ²
Conductor cross section AWG min.	24
Conductor cross section AWG max.	16
Stripping length	10 mm

General

Mounting type	Single-hole mounting
Net weight	370.2 g
Degree of pollution	2
Note	Degree of protection when installed
Wireless licenses	EU, more countries in e-shop
Wireless licences	Belgium
	Bulgaria
	Denmark
	Germany
	Estonia
	Finland
	France
	Greece
	Great Britain
	Ireland
	Italy
	Latvia
	Liechtenstein
	Lithuania
	Luxembourg
	Malta
	Netherlands

Wireless module - FL WLAN 1100 - 2702534

Technical data

General

	Norway
	Austria
	Poland
	Portugal
	Romania
	Sweden
	Switzerland
	Slovakia
	Slovenia
	Spain
	Czech Republic
	Hungary
	Cyprus (rep.)
	China
	Japan
	South Korea

Standards and Regulations

Mechanical tests	Shock in acc. with EN 60068-2-27/IEC 60068-2-27 30g, 11 ms half-sine shock pulse
	Vibration resistance in acc. with EN 60068-2-6/IEC 60068-2-6 5g, 10 ... 150 Hz
	Continuous shock according to EN 60068-2-27/IEC 60068-2-27 10g, 16 ms, 6000 shocks
	Broadband noise according to EN 60068-2-64 Category 1, Class A
Standards/regulations	EN 61000-4-2
Contact discharge	± 4 kV
Indirect discharge	± 6 kV
Standards/regulations	EN 61000-4-3
Frequency range	80 MHz ... 1000 MHz
Test field strength	10 V/m
Frequency range	1000 MHz ... 6000 MHz
Test field strength	3 V/m
Standards/regulations	EN 61000-4-4
Comments	± 2.2 kV
Standards/regulations	EN 61000-4-5
Signal	± 0.5 kV (symmetrical)
	± 1 kV (asymmetrical)
Standards/regulations	EN 55022
Test result	Class B
Standards/regulations	EN 61000-4-6
Frequency range	0.15 MHz ... 80 MHz
Voltage	10 V

Wireless module - FL WLAN 1100 - 2702534

Technical data

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
-------------------	----------------

Classifications

eCl@ss

eCl@ss 4.0	24010504
eCl@ss 4.1	24010504
eCl@ss 5.0	19030112
eCl@ss 5.1	19030100
eCl@ss 6.0	19170200
eCl@ss 7.0	19170201
eCl@ss 8.0	19170201
eCl@ss 9.0	19170201
eCl@ss 10.0.1	19170501

ETIM

ETIM 3.0	EC000817
ETIM 4.0	EC000816
ETIM 5.0	EC000816
ETIM 6.0	EC000816
ETIM 7.0	EC000816

UNSPSC

UNSPSC 6.01	43172710
UNSPSC 7.0901	43223108
UNSPSC 11	43172710
UNSPSC 12.01	43223108
UNSPSC 13.2	43223108

Approvals

EAC / KC /

Approval details

EAC

KC

Accessories

Adapter

Wireless module - FL WLAN 1100 - 2702534

Accessories

FL M32 ADAPTER - 2702544



Data plug

CUC-IND-C1ZNI-S/R4IE8 - 1421607



PCB plug

FMC 1,5/ 3-STF-3,5 - 1966101



Patch cable

FL CAT5 PATCH 1,5 - 2832221



Drawings

Phoenix Contact 2019 © - all rights reserved
<http://www.phoenixcontact.com>