

# Safety data sheet

## according to 1907/2006/EC, Article 31

Printing date 02.10.2018

Version: 1.00

Revision: 17.07.2018

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1 Product identifier

**Trade name:** GLORIA® TOP FOAM Car shampoo

**Article number:** 001160.0000

#### 1.2 Relevant identified uses of the substance or mixture and uses advised against

##### Sector of Use

SU21 Consumer uses: Private households / general public / consumers

SU22 Professional uses: Public domain (administration, education, entertainment, services, craftsmen)

**Product category** PC35 Washing and cleaning products (including solvent based products)

**Application of the substance / the mixture** Car care product

#### 1.3 Details of the supplier of the safety data sheet

##### Manufacturer/Supplier:

GLORIA Haus- und Gartengeräte GmbH

Därmanbusch 7

D-58456 Witten

Phone: +49 (0) 2302 / 700-0

Fax: +49 (0) 2302 / 700-446

##### Further information obtainable from:

E-mail: [info@gloria-garten.com](mailto:info@gloria-garten.com)

Phone: +49 (0) 2302 / 700-0

#### 1.4 Emergency telephone number: Emergency Phone Munich Tel.: +49 (0)89 19240

### SECTION 2: Hazards identification

#### 2.1 Classification of the substance or mixture

**Classification according to Regulation (EC) No 1272/2008**

Eye Irrit. 2 H319 Causes serious eye irritation.

#### 2.2 Label elements

**Labelling according to Regulation (EC) No 1272/2008**

The product is classified and labelled according to the CLP regulation.

##### Hazard pictograms



GHS07

**Signal word** Warning

##### Hazard statements

H319 Causes serious eye irritation.

##### Precautionary statements

P101 If medical advice is needed, have product container or label at hand.

P102 Keep out of reach of children.

P280 Wear eye protection.

P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P337+P313 If eye irritation persists: Get medical advice/attention.

P501 Dispose of contents/container in accordance with local/regional/national/international regulations.

#### 2.3 Other hazards

##### Results of PBT and vPvB assessment

**PBT:** Not applicable.

**vPvB:** Not applicable.

### SECTION 3: Composition/information on ingredients

#### 3.2 Mixtures

**Description:** Aqueous tenside solution.

(Contd. on page 2)

GB

# Safety data sheet

## according to 1907/2006/EC, Article 31

Printing date 02.10.2018

Version: 1.00

Revision: 17.07.2018

**Trade name: GLORIA® TOP FOAM Car shampoo**

(Contd. of page 1)

**Dangerous components:**

CAS: 68891-38-3 NLP: 500-234-8 Reg.nr.: 01-2119488639-16-xxxx	alcohols, C12-14, ethoxylated, sulfates, sodium salts ☠ Eye Dam. 1, H318; ☠ Skin Irrit. 2, H315; Aquatic Chronic 3, H412	5-<10%
CAS: 107-98-2 EINECS: 203-539-1 Reg.nr.: 01-2119457435-35-xxxx	1-Methoxy-2-propanol ☠ Flam. Liq. 3, H226; ☠ STOT SE 3, H336	3-<5%
CAS: 308062-28-4 Reg.nr.: 01-2119490061-47-xxxx	Amines, C12-14 (even numbered)-alkyldimethyl, N-oxides ☠ Eye Dam. 1, H318; ☠ Aquatic Acute 1, H400; Aquatic Chronic 2, H411; ☠ Acute Tox. 4, H302; Skin Irrit. 2, H315	<0.25%

**Regulation (EC) No 648/2004 on detergents / Labelling for contents**

anionic surfactants	≥5 - <15%
perfumes, limonene, linalool, methylisothiazolinone, benzisothiazolinone, sodium pyrrhione	

**Additional information:** For the wording of the listed hazard phrases refer to section 16.**SECTION 4: First aid measures****4.1 Description of first aid measures****General information:** Remove soiled clothing**After inhalation:** Supply fresh air; consult doctor in case of complaints.**After skin contact:**

Generally the product does not irritate the skin.

Wash the areas of skin affected with water and a mild detergent.

**After eye contact:** Rinse opened eye for several minutes under running water. Then consult a doctor.**After swallowing:**

Rinse out mouth and then drink plenty of water.

Do not induce vomiting; call for medical help immediately.

**4.2 Most important symptoms and effects, both acute and delayed** Eye irritation**4.3 Indication of any immediate medical attention and special treatment needed**

Treatment in accordance with the doctor's assessment of the patient's condition. Symptomatic treatment.

**SECTION 5: Firefighting measures****5.1 Extinguishing media****Suitable extinguishing agents:** Use fire extinguishing methods suitable to surrounding conditions.**5.2 Special hazards arising from the substance or mixture** No further relevant information available.**5.3 Advice for firefighters****Protective equipment:** The normal measures for firefighting are to be taken.**SECTION 6: Accidental release measures****6.1 Personal precautions, protective equipment and emergency procedures** Ensure adequate ventilation**6.2 Environmental precautions:**

Do not allow to penetrate the ground/soil.

Do not allow to enter sewers/ surface or ground water.

**6.3 Methods and material for containment and cleaning up:**

Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).

Dispose contaminated material as waste according to item 13.

**6.4 Reference to other sections**

See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

**SECTION 7: Handling and storage****7.1 Precautions for safe handling** No special precautions are necessary if used correctly.

(Contd. on page 3)

## Safety data sheet

### according to 1907/2006/EC, Article 31

Printing date 02.10.2018

Version: 1.00

Revision: 17.07.2018

Trade name: GLORIA® TOP FOAM Car shampoo

(Contd. of page 2)

**Information about fire - and explosion protection:** No special measures required.**7.2 Conditions for safe storage, including any incompatibilities****Storage:****Requirements to be met by storerooms and receptacles:** Prevent any seepage into the ground.**Information about storage in one common storage facility:** Store away from foodstuffs.**Further information about storage conditions:**

Protect from frost.

Recommended storage temperature: 20 °C.

**7.3 Specific end use(s)** No further relevant information available.

## SECTION 8: Exposure controls/personal protection

**8.1 Control parameters****Ingredients with limit values that require monitoring at the workplace:****CAS: 107-98-2 1-Methoxy-2-propanol**

WEL (Great Britain)	Short-term value:	560 mg/m <sup>3</sup> , 150 ppm
	Long-term value:	375 mg/m <sup>3</sup> , 100 ppm
Sk		
IOELV (EU)	Short-term value:	568 mg/m <sup>3</sup> , 150 ppm
	Long-term value:	375 mg/m <sup>3</sup> , 100 ppm
Skin		

**Regulatory information**

WEL (Great Britain): EH40/2011

IOELV (EU): (EU) 2017/164

**DNELs****CAS: 68891-38-3 alcohols, C12-14, ethoxylated, sulfates, sodium salts**

Oral	DNEL	15 mg/kg (VL)
Dermal	DNEL	1,650 mg/kg (VL)
		2,750 mg/kg (worker long-term)
Inhalative	DNEL	52 mg/m <sup>3</sup> (VL)
	DNEL	175 mg/m <sup>3</sup> (worker long-term)

**CAS: 107-98-2 1-Methoxy-2-propanol**

Oral	DNEL	3.3 mg/kg (consumer) (long-term / systemic effects)
Dermal	DNEL	18.1 mg/kg (consumer) (long-term / systemic effects)
		50.6 mg/kg (worker) (long-term / systemic effects)
Inhalative	DNEL	43.9 mg/m <sup>3</sup> (consumer) (long-term / systemic effects)
		553.5 mg/m <sup>3</sup> (worker) (short-term / local effects)
		369 mg/m <sup>3</sup> (worker) (long-term / systemic effects)

**CAS: 308062-28-4 Amines, C12-14 (even numbered)-alkyldimethyl, N-oxides**

Oral	DNEL	0.44 mg/kg bw/day (consumer) (longterm / systemic effects)
Dermal	DNEL	5.5 mg/kg bw/day (consumer) (longterm / systemic effects)
		11 mg/kg bw/day (worker) (longtime / systemic effects)
Inhalative	DNEL	1.53 mg/m <sup>3</sup> (consumer) (longterm / systemic effects)
		6.2 mg/m <sup>3</sup> (worker) (longterm / systemic effects)

**PNECs****CAS: 68891-38-3 alcohols, C12-14, ethoxylated, sulfates, sodium salts**

PNEC	10,000 mg/l (sewage plant)
	0.071 mg/l (sporadic release)
	0.24 mg/l (water (fresh water))
	0.024 mg/l (water (sea water))
PNEC	7.5 mg/kg (gro)
	0.9168 mg/kg (sediment (fresh water))
	0.09168 mg/kg (sediment (sea water))

(Contd. on page 4)

# Safety data sheet

## according to 1907/2006/EC, Article 31

Printing date 02.10.2018

Version: 1.00

Revision: 17.07.2018

Trade name: GLORIA® TOP FOAM Car shampoo

(Contd. of page 3)

**CAS: 107-98-2 1-Methoxy-2-propanol**

PNEC	100 mg/l (STP)
	100 mg/l (water (intermittent release))
	10 mg/l (water (fresh water))
	1 mg/l (water (sea water))
PNEC	2.47 mg/kg (gro)
	41.6 mg/kg (sediment (fresh water))
	4.17 mg/kg (sediment (sea water))

**CAS: 308062-28-4 Amines, C12-14 (even numbered)-alkyldimethyl, N-oxides**

PNEC	0.0335 mg/l (water (intermittent release))
	0.0335 mg/l (water (fresh water))
	0.00335 mg/l (water (sea water))
PNEC	24 mg/kg (STP)
	5.24 mg/kg (sediment (fresh water))
	0.524 mg/kg (sediment (sea water))
	1.02 mg/kg (soil)

**Additional information:** The lists valid during the making were used as basis.

**8.2 Exposure controls****Suitable technical control devices**

Ensure good ventilation. This can be achieved by localised extraction or general ventilation. If this is not sufficient to keep the concentration below the occupational exposure limit, suitable breathing protection is to be worn.

**Personal protective equipment:****General protective and hygienic measures:**

The usual precautionary measures are to be adhered to when handling chemicals.

Keep away from foodstuffs, beverages and feed.

Wash hands before breaks and at the end of work.

**Respiratory protection:**

Not required in normal cases

Ensure good ventilation/exhaustion at the workplace.

**Protection of hands:** Not required in normal cases.

**Eye protection:**

Safety glasses

[EN 166]

## SECTION 9: Physical and chemical properties

**9.1 Information on basic physical and chemical properties****General Information****Appearance:**

<b>Form:</b>	Fluid
<b>Colour:</b>	Colourless
<b>Odour:</b>	Characteristic
<b>Odour threshold:</b>	Not determined.

<b>pH-value at 20 °C:</b>	7.0 - 8.0
---------------------------	-----------

**Change in condition**

<b>Melting point/freezing point:</b>	Undetermined.
<b>Initial boiling point and boiling range:</b>	100 - 120 °C

<b>Flash point:</b>	Not applicable.
---------------------	-----------------

<b>Flammability (solid, gas):</b>	Not applicable.
-----------------------------------	-----------------

<b>Decomposition temperature:</b>	Not determined.
-----------------------------------	-----------------

<b>Auto-ignition temperature:</b>	Product is not selfigniting.
-----------------------------------	------------------------------

(Contd. on page 5)

GB

# Safety data sheet

## according to 1907/2006/EC, Article 31

Printing date 02.10.2018

Version: 1.00

Revision: 17.07.2018

Trade name: GLORIA® TOP FOAM Car shampoo

(Contd. of page 4)

**Explosive properties:** Product does not present an explosion hazard.

**Explosion limits:**

**Lower:** Not determined.

**Upper:** Not determined.

**Vapour pressure:** Not determined.

**Density at 20 °C:** 1.01 - 1.02 g/cm<sup>3</sup>

**Relative density** Not determined.

**Vapour density** Not determined.

**Evaporation rate** Not determined.

**Solubility in / Miscibility with water:**

Fully miscible.

**Partition coefficient: n-octanol/water:** Not determined.

**Viscosity:**

**Flow time at 20 °C** 10 - 15 s (DIN EN ISO 2431/4mm)

**9.2 Other information** No further relevant information available.

### SECTION 10: Stability and reactivity

**10.1 Reactivity** No dangerous reactions known.

**10.2 Chemical stability** Stable under normal conditions.

**10.3 Possibility of hazardous reactions** No dangerous reactions known.

**10.4 Conditions to avoid** See Section 7 for information on safe handling.

**10.5 Incompatible materials:** No further relevant information available.

**10.6 Hazardous decomposition products:** No dangerous decomposition products known.

### SECTION 11: Toxicological information

**11.1 Information on toxicological effects** There are no toxicological findings on this mixture.

**Acute toxicity** Based on available data, the classification criteria are not met.

**LD/LC50 values relevant for classification:**

**CAS: 68891-38-3 alcohols, C12-14, ethoxylated, sulfates, sodium salts**

Oral LD50 >5,000 mg/kg (rat) (OECD 401)

Dermal LD50 >5,000 mg/kg (rat) (OECD 402)

**CAS: 107-98-2 1-Methoxy-2-propanol**

Oral LD50 4,016 mg/kg (rat)

Dermal LD50 >2,000 mg/kg (rat)

Inhalative LC0 / 6h >7,000 ppm (rat)

**CAS: 308062-28-4 Amines, C12-14 (even numbered)-alkyldimethyl, N-oxides**

Oral LD50 1,064 mg/kg (rat)

**Primary irritant effect:****Skin corrosion/irritation**

On the basis of the available data, the classification criteria are not complied with (Conventional Method).

**Serious eye damage/irritation**

Causes serious eye irritation.

**Values relevant for classification:**

**68891-38-3 alcohols, C12-14, ethoxylated, sulfates, sodium salts (> 1 < 2.5 mol EO):**

Specific concentration limits [SCL] (ECHA)

≥ 5.0% < 10.0% Eye Irrit. 2 | ≥ 10.0% Eye Damage 1

**Respiratory or skin sensitisation**

On the basis of the available data, the classification criteria are not complied with (Conventional Method).

(Contd. on page 6)

GB

## Safety data sheet

### according to 1907/2006/EC, Article 31

Printing date 02.10.2018

Version: 1.00

Revision: 17.07.2018

Trade name: GLORIA® TOP FOAM Car shampoo

(Contd. of page 5)

**Repeated dose toxicity****CAS: 308062-28-4 Amines, C12-14 (even numbered)-alkyldimethyl, N-oxides**

Oral	NOAEL	88 mg/kg (rat) (subchronic effects)
Dermal	LOAEL	0.045 mg/cm <sup>2</sup> (mouse) (subchronic effects)

**CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)**

None of the ingredients are known to have effects which are carcinogenic, mutagenic or harmful to reproduction.

**Germ cell mutagenicity** Based on available data, the classification criteria are not met.

**Carcinogenicity** Based on available data, the classification criteria are not met.

**Reproductive toxicity** Based on available data, the classification criteria are not met.

**STOT-single exposure** Based on available data, the classification criteria are not met.

**STOT-repeated exposure** Based on available data, the classification criteria are not met.

**Aspiration hazard** Based on available data, the classification criteria are not met.

## SECTION 12: Ecological information

**12.1 Toxicity** There are no ecotoxicological data available on this mixture.

**Aquatic toxicity:****CAS: 68891-38-3 alcohols, C12-14, ethoxylated, sulfates, sodium salts**

LC 50	>10-≤100 mg/l (Leuciscus idus) (DIN EN ISO 7346-2)
EC0	>100 mg/l (bacteria) (OECD 209)
EC50	>100 mg/l (Scenedesmus subspicatus) (OECD 201)
	>10-100 mg/l (Daphnia magna) (OECD 202)
NOEC	>1-10 mg/l (Leuciscus idus)

**CAS: 107-98-2 1-Methoxy-2-propanol**

LC50 / 96h	>6,800 mg/l (Leuciscus idus) (DIN38412)
LC50 / 48h	23,300 mg/l (Daphnia magna)
EC50	>1,000 mg/l (Pseudokirchneriella subcapitata) (7d)
EC50/3h	>1,000 mg/l (activated sludge) (OECD 209)

**CAS: 308062-28-4 Amines, C12-14 (even numbered)-alkyldimethyl, N-oxides**

LC50 / 96h	2.67 mg/l (fish)
EC50	3.1 mg/l (waterflea /Wasserfloh)
IC 50	0.143 mg/l (seaweed (Seegras))

**12.2 Persistence and degradability**

The surface-active substances contained in the product meet the requirement of the EU Detergent Regulation ( EC/648/2004 ) for ultimate biodegradability for surfactants in detergents.

**CAS: 107-98-2 1-Methoxy-2-propanol**

Biodegradation	90-100 % (OECD 301E)
----------------	----------------------

**12.3 Bioaccumulative potential****CAS: 107-98-2 1-Methoxy-2-propanol**

log Kow	≤0.43 log Kow (25°C)
---------	----------------------

**12.4 Mobility in soil** No further relevant information available.

**Additional ecological information:**

**General notes:** The product may not be released into the environment without control.

**12.5 Results of PBT and vPvB assessment**

**PBT:** Not applicable.

**vPvB:** Not applicable.

**12.6 Other adverse effects** No further relevant information available.

GB

(Contd. on page 7)



## Safety data sheet

### according to 1907/2006/EC, Article 31

Printing date 02.10.2018

Version: 1.00

Revision: 17.07.2018

Trade name: GLORIA® TOP FOAM Car shampoo

(Contd. of page 6)

### SECTION 13: Disposal considerations

#### 13.1 Waste treatment methods

**Recommendation** Waste must be disposed of while observing the local, official regulations.

#### European waste catalogue

1) Disposal / product

2) Disposal / contaminated packaging

20 01 30	detergents other than those mentioned in 20 01 29
15 01 02	plastic packaging

### SECTION 14: Transport information

#### 14.1 UN-Number

ADR, IMDG, IATA Void

#### 14.2 UN proper shipping name

ADR, IMDG, IATA Void

#### 14.3 Transport hazard class(es)

ADR, ADN, IMDG, IATA

Class Void

#### 14.4 Packing group

ADR, IMDG, IATA Void

#### 14.5 Environmental hazards:

Marine pollutant: No

#### 14.6 Special precautions for user

Not applicable.

UN "Model Regulation": Void

### SECTION 15: Regulatory information

#### 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

##### National regulations:

##### Information about limitation of use:

Employment restrictions concerning pregnant and lactating women must be observed.

Employment restrictions concerning juveniles must be observed.

**15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

### SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

#### Relevant phrases

H226 Flammable liquid and vapour.

H302 Harmful if swallowed.

H315 Causes skin irritation.

H318 Causes serious eye damage.

H336 May cause drowsiness or dizziness.

H400 Very toxic to aquatic life.

H411 Toxic to aquatic life with long lasting effects.

H412 Harmful to aquatic life with long lasting effects.

#### Abbreviations and acronyms:

NOEL = No Observed Effect Level

NOEC = No Observed Effect Concentration

LC = lethal Concentration

EC50 = half maximal effective concentration

log POW = Octanol / water partition coefficient

GHS: Globally Harmonized System of Classification and Labelling of Chemicals

(Contd. on page 8)

GB

## Safety data sheet

### according to 1907/2006/EC, Article 31

Printing date 02.10.2018

Version: 1.00

Revision: 17.07.2018

**Trade name: GLORIA® TOP FOAM Car shampoo**

(Contd. of page 7)

ATE: acute toxicity estimate

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

DNEL: Derived No-Effect Level (REACH)

PNEC: Predicted No-Effect Concentration (REACH)

LC50: Lethal concentration, 50 percent

LD50: Lethal dose, 50 percent

IOELV = indicative occupational exposure limit values

Flam. Liq. 3: Flammable liquids – Category 3

Acute Tox. 4: Acute toxicity – Category 4

Skin Irrit. 2: Skin corrosion/irritation – Category 2

Eye Dam. 1: Serious eye damage/eye irritation – Category 1

Eye Irrit. 2: Serious eye damage/eye irritation – Category 2

STOT SE 3: Specific target organ toxicity (single exposure) – Category 3

Aquatic Acute 1: Hazardous to the aquatic environment - acute aquatic hazard – Category 1

Aquatic Chronic 2: Hazardous to the aquatic environment - long-term aquatic hazard – Category 2

Aquatic Chronic 3: Hazardous to the aquatic environment - long-term aquatic hazard – Category 3

GB