


PROPRIETARY RIGHTS ARE CLAIMED FOR THE MATERIAL DISCLOSED IN THIS DRAWING.

TYP. WALL THICKNESS = 1.8

LTR.	REVISIONS	DATE
✧	*****	00-00-98

SEAL OPTIONS



SEAL THICKNESS = .8




SEE VIEW "B"

SECTION A-A


SEAL NO. 3 SHOWN





NO. 1
Wire Gages
18 - 10



NO. 2
Cable Gages
8 - 2




NO. 3
Cable Gages
2 - 2/0



VIEW "B"
SCALE: 3" = 1"

TOLERANCE UNLESS OTHERWISE SPECIFIED: $\pm 0.030"/\pm 0.8mm$
RADIAL DIAMETERS TO BE MEASURED OVER MANDRELS,
RING GAGES OR PIN GAGES OF SUITABLE SIZE

VTE Material Part No: 1101650102
Material: RED PVC
Material Part No: 9812-65-RED683
Max. Operating Temp: 105 C
Shore Durometer "A" 10 SEC. 67/62
Specific Gravity: 1.34
Ult. Elongation %: 475
Brittle Temp: -44 C
Tensile Strength PSI: 1547 PSI
Dielectric Strength, v./ml: 540
U.L. Rating: 94 V2
MEETS: FMVSS.302



REF:	DATE: 3-20-98	DRN BY: JC	WEIGHT: .022 LBS. / 9.75 G
TITLE: TERMINAL INSULATOR CAP		PART NO. 220N3V02	
MATERIAL:		DRG CLASS	
COLOR:			