

### ■ Features

- SIP7 package with international standard pinout
- Operating temperature range -40 ~ +85°C
- Medical safety approved (1xMOPP/2xMOOP) according to ANSI/AAMI ES60601-1
- Low patient leakage current <2μA
- Protection: Short circuit(3 second max.)
- 6KVDC or 4.2KVAC high I/O isolation (Reinforced isolation)
- Low cost
- 3 years warranty

### ■ Applications

- Medical devices
- Medical oxygen monitor
- CT scanning
- Medical carts
- Oral care equipment

### ■ GTIN CODE


MW Search: <https://www.meanwell.com/serviceGTIN.aspx>

### ■ Description

MDS01 and MDD01 series are 1W isolated and unregulated module type medical grade DC-DC converter with SIP7 package. It features international standard pins, a high efficiency up to 83%, wide working temperature range -40~+85°C, 6KVDC or 4.2KVAC I/P-O/P high isolation voltage, short circuit protection, etc. The models account for different input voltage 5V/12V/24V±10%, and various output voltage, 3.3V/5V/12V/15V for single output and ±5V/±9V/±12V/±15V for dual outputs, which are suitable for medical systems, ultra low leakage current.

### ■ Model Encoding

**MDS01L-12**





| MODEL SELECTION TABLE |                              |               |           |                |                |                   |                       |
|-----------------------|------------------------------|---------------|-----------|----------------|----------------|-------------------|-----------------------|
| ORDER NO.             | INPUT                        |               |           | OUTPUT         |                | EFFICIENCY (TYP.) | CAPACITOR LOAD (MAX.) |
|                       | INPUT VOLTAGE (RANGE)        | INPUT CURRENT |           | OUTPUT VOLTAGE | OUTPUT CURRENT |                   |                       |
|                       |                              | NO LOAD       | FULL LOAD |                |                |                   |                       |
| MDS01L-03             | Normal 5V<br>(4.5 ~ 5.5V)    | 25mA          | 260mA     | 3.3V           | 31 ~ 303mA     | 73%               | 1000μF                |
| MDS01L-05             |                              | 25mA          | 260mA     | 5V             | 20 ~ 200mA     | 78%               | 1000μF                |
| MDS01L-12             |                              | 40mA          | 260mA     | 12V            | 9 ~ 84mA       | 77%               | 470μF                 |
| MDS01L-15             |                              | 45mA          | 265mA     | 15V            | 7 ~ 67mA       | 75%               | 470μF                 |
| MDD01L-05             |                              | 25mA          | 260mA     | ±5V            | ±10 ~ 100mA    | 79%               | *470μF                |
| MDD01L-09             |                              | 35mA          | 260mA     | ±9V            | ±6 ~ 56mA      | 81%               | *470μF                |
| MDD01L-12             |                              | 40mA          | 265mA     | ±12V           | ±5 ~ 42mA      | 77%               | *220μF                |
| MDD01L-15             |                              | 45mA          | 275mA     | ±15V           | ±4 ~ 34mA      | 77%               | *220μF                |
| MDS01M-05             | Normal 12V<br>(10.8 ~ 13.2V) | 15mA          | 105mA     | 5V             | 20 ~ 200mA     | 78%               | 1000μF                |
| MDS01M-12             |                              | 15mA          | 105mA     | 12V            | 9 ~ 84mA       | 82%               | 470μF                 |
| MDS01M-15             |                              | 15mA          | 105mA     | 15V            | 7 ~ 67mA       | 83%               | 470μF                 |
| MDD01M-05             |                              | 14mA          | 105mA     | ±5V            | ±10 ~ 100mA    | 78%               | *470μF                |
| MDD01M-09             |                              | 14mA          | 105mA     | ±9V            | ±6 ~ 56mA      | 82%               | *470μF                |
| MDD01M-12             |                              | 22mA          | 114mA     | ±12V           | ±5 ~ 42mA      | 75%               | *220μF                |
| MDD01M-15             |                              | 22mA          | 114mA     | ±15V           | ±4 ~ 34mA      | 76%               | *220μF                |
| MDS01N-05             | Normal 24V<br>(21.6 ~ 26.4V) | 9mA           | 55mA      | 5V             | 20 ~ 200mA     | 77%               | 1000μF                |
| MDS01N-12             |                              | 9mA           | 55mA      | 12V            | 9 ~ 84mA       | 79%               | 470μF                 |
| MDS01N-15             |                              | 9mA           | 55mA      | 15V            | 7 ~ 67mA       | 79%               | 470μF                 |
| MDD01N-05             |                              | 9mA           | 55mA      | ±5V            | ±10 ~ 100mA    | 77%               | *470μF                |
| MDD01N-09             |                              | 9mA           | 55mA      | ±9V            | ±6 ~ 56mA      | 79%               | *470μF                |
| MDD01N-12             |                              | 10mA          | 56mA      | ±12V           | ±5 ~ 42mA      | 77%               | *220μF                |
| MDD01N-15             |                              | 11mA          | 57mA      | ±15V           | ±4 ~ 34mA      | 77%               | *220μF                |


\* For each output



| SPECIFICATION                             |   |  |                        |                          |
|---|---|--|------------------------|--------------------------|
| INPUT                                     | VOLTAGE RANGE   | L: 4.5 ~ 5.5Vdc<br>M: 10.8 ~ 13.2Vdc<br>N: 21.6 ~ 26.4Vdc                            |                        |                          |
|   | SURGE VOLTAGE (100ms max.)  | 5Vin models : 9Vdc<br>12Vin models : 18Vdc<br>24Vin models : 30Vdc                   |                        |                          |
|   | FILTER  | Internal capacitor   |                        |                          |
|   | PROTECTION  | Fuse recommended. 500mA Slow-Blow Type for all models                                |                        |                          |
| OUTPUT                                    | VOLTAGE ACCURACY  | ±5.0%  |                        |                          |
|   | RATED POWER   | 1W   |                        |                          |
|   | RIPPLE & NOISE <small>Note.2</small>  | 75mVp-p  |                        |                          |
|   | LINE REGULATION <small>Note.3</small>   | 1.2% for 1% input variation  |                        |                          |
|   | LOAD REGULATION <small>Note.4</small>   | ±10%   |                        |                          |
|   | SWITCHING FREQUENCY (Typ.)  | 100KHz   |                        |                          |
| PROTECTION                                | SHORT CIRCUIT   | 3 second max.  |                        |                          |
| ENVIRONMENT                               | COOLING   | Free-air convection  |                        |                          |
|   | WORKING TEMP.   | -40 ~ +85°C (Refer to "Derating Curve")  |                        |                          |
|   | WORKING HUMIDITY  | 20% ~ 90% RH non-condensing  |                        |                          |
|   | STORAGE TEMP., HUMIDITY   | -55 ~ +125°C, 10 ~ 95% RH non-condensing   |                        |                          |
|   | TEMP. COEFFICIENT   | 0.02% / °C (0 ~ 85°C)  |                        |                          |
|   | SOLDERING TEMPERATURE   | 1.5mm from case of 1 ~ 3sec./260°C max.  |                        |                          |
|   | VIBRATION   | 10 ~ 500Hz, 2G 10min./1cycle, period for 60min. each along X, Y, Z axes              |                        |                          |
| SAFETY & EMC<br>( <small>Note.6</small> ) | SAFETY STANDARDS  | UL60601-1, EAC TP TC 020/2011 approved   |                        |                          |
|   | WITHSTAND VOLTAGE   | I/P-O/P:6KVDC or 4.2KVAC   |                        |                          |
|   | ISOLATION RESISTANCE  | I/P-O/P:100M Ohms / 500VDC / 25°C / 70% RH   |                        |                          |
|   | ISOLATION LEVEL   | Primary-secondary: 1xMOPP / 2xMOOP when system input voltage is with 250VAC, 50/60Hz |                        |                          |
|   | ISOLATION CAPACITANCE (Typ.)  | 5pF  |                        |                          |
|   | EMC EMISSION  | <b>Parameter</b>   | <b>Standard</b>        | <b>Test Level / Note</b> |
|   |   | Conducted  | BS EN/EN55011(CISPR11) | Class B                  |
|   |   | Radiated   | BS EN/EN55011(CISPR11) | Class B                  |
|   | EMC IMMUNITY  | <b>Parameter</b>   | <b>Standard</b>        | <b>Test Level / Note</b> |
|   |   | ESD  | BS EN/EN61000-4-2      | Level 2, ±8KV contact    |
| OTHERS                                    | MTBF  | 3500Khrs MIL-HDBK-217F(25°C)   |                        |                          |
|   | DIMENSION (L*W*H)   | 19.5*9.8*12.5mm (0.77*0.386*0.492 inch)  |                        |                          |
|   | CASE MATERIAL   | Non-Conductive black plastic (UL 94V-0 rated)  |                        |                          |
|   | PACKING   | 4.2g ; 25pcs/per tube, 3000pcs/120 tube/per carton                                   |                        |                          |
| NOTE                                      | <p>1.All parameters are specified at normal input(L:5Vdc, M:12Vdc, N:24Vdc), rated load, 25°C 70% RH ambient.</p> <p>2.Ripple &amp; noise are measured at 20MHz by using a 12" twisted pair terminated with a 0.1µf &amp; 47µf capacitor.</p> <p>3.Line regulation is measured from low line to high line at rated load.</p> <p>4.Load regulation is measured from 10% to 100% rated load.</p> <p>5.Patient leakage current(2µA max.) and reinforced isolation is based on a 250VAC, 50/60Hz system input voltage.</p> <p>6.The final equipment must be re-confirm that it still meet EMC directives. For guidance on how to perform these EMC tests, please refer to "EMI testing of component power supplies."(as available on <a href="http://www.meanwell.com">http://www.meanwell.com</a>)</p> <p>※ Product Liability Disclaimer : For detailed information, please refer to <a href="https://www.meanwell.com/serviceDisclaimer.aspx">https://www.meanwell.com/serviceDisclaimer.aspx</a></p> |  |                        |                          |

**Mechanical Specification**

- All dimensions in mm(inch)
- Tolerance:  $x.x \pm 0.25\text{mm}(x.xx \pm 0.01\text{"})$   
 $x.xx \pm 0.10\text{mm}(x.xxx \pm 0.004\text{"})$
- Pin pitch tolerance:  $\pm 0.05\text{mm}(\pm 0.002\text{"})$




**Plug Assignment**

| Pin-Out |                       |                     |
|---------|-----------------------|---------------------|
| Pin No. | MDS01 (Single output) | MDD01 (Dual output) |
| 1       | +Vin                  | +Vin                |
| 2       | -Vin                  | -Vin                |
| 5       | -Vout                 | -Vout               |
| 6       | No pin                | Common              |
| 7       | +Vout                 | +Vout               |

**EMC Suggestion**

EMC typical recommended circuit (Class B)



Recommended typical circuit parameters:


| Input voltage (V) |        | 3.3/5/12/15/24 |
|-------------------|--------|----------------|
| EMI               | C1, C2 | 4.7µF/50V      |
|                   | C3     | See table 2    |
|                   | LDM    | 6.8µH          |

Table 1




| Single Vout | C3(µF) | Dual Vout  | C3(µF) |
|-------------|--------|------------|--------|
| 3.3/5V      | 10µF   | ±5V        | 4.7µF  |
| 12V         | 2.2µF  | ±9V        | 2.2µF  |
| 15V         | 1µF    | ±12V / 15V | 1µF    |

Table 2

### Derating Curve



### Packing

| Standard Tube Packing   | MPQ Per Tube (PCS) | One Tube G.W. | Max. Q'TY/ Carton(PCS) | One Carton G.W. |
|---|--------------------|---------------|------------------------|-----------------|
| <p>Unit : mm</p>  <p>Product</p> <p>Tube Plugs</p>  <p>Tube pattern</p>  <p>CARTON<br/>L600 x W285 x H225</p> | 25                 | 136g          | 3000                   | 18.5Kg          |

### Installation Manual

Please refer to : <http://www.meanwell.com/manual.html>