



**Product: BRS20-8TX-EEC**

**Configurator: BOBCAT**

### Configurator Description

The Hirschmann BOBCAT Switch is the first of its kind to enable real-time communication using TSN. To effectively support the increasing real-time communication requirements in industrial settings, a strong Ethernet network backbone is essential. This compact managed switches allow for expanded bandwidth capabilities by adjusting your SFPs from 1 to 2.5 Gigabit – requiring no change to the appliance.

### Technical Specifications

#### Product description

|                        |   |
|------------------------|---|
| Type                   | BRS20-8TX-EEC (Product code: BRS20-08009999-TTCY99HHSESXX.X.XX)           |
| Description            | Managed Industrial Switch for DIN Rail, fanless design Fast Ethernet Type |
| Part Number            | 942170012   |
| Port type and quantity | 8 Ports in total: 8x 10/100BASE TX / RJ45                                 |

#### More Interfaces

|   |                                   |
|---|-----------------------------------|
| Power supply/signaling contact          | 1 x plug-in terminal block, 6-pin |
| Local Management and Device Replacement | USB-C                             |
| Digital Input                           | 1 x plug-in terminal block, 2-pin |

#### Network size - length of cable

|                   |           |
|-------------------|-----------|
| Twisted pair (TP) | 0 - 100 m |
|-------------------|-----------|

#### Network size - cascading

|                        |     |
|------------------------|-----|
| Line - / star topology | any |
|------------------------|-----|

#### Power requirements

|                   |                        |
|-------------------|------------------------|
| Operating voltage | 2 x 12 V DC ... 24 VDC |
|-------------------|------------------------|

#### Software

|                      |  |
|----------------------|--|
| Switching            | Independent VLAN Learning, Fast Aging, Static Unicast/Multicast Address Entries, QoS / Port Prioritization (802.1D/p), TOS/DSCP Prioritization, Interface Trust Mode, CoS Queue Management, Flow Control (802.3X), Egress Interface Shaping, Ingress Storm Protection, Jumbo Frames, VLAN (802.1Q), GARP VLAN Registration Protocol (GVRP), Voice VLAN, GARP Multicast Registration Protocol (GMRP), IGMP Snooping/Querier per VLAN (v1/v2/v3), Unknown Multicast Filtering, Multiple VLAN Registration Protocol (MVRP), Multiple MAC Registration Protocol (MMRP), Multiple Registration Protocol (MRP) |
| Redundancy           | HIPER-Ring (Ring Switch), Link Aggregation with LACP, Link Backup, Media Redundancy Protocol (MRP) (IEC62439-2), Redundant Network Coupling, RSTP 802.1D-2004 (IEC62439-1), RSTP Guards  |
| Management           | Dual Software Image Support, TFTP, SFTP, SCP, LLDP (802.1AB), LLDP-MED, SSHv2, HTTP, HTTPS, Traps, SNMP v1/v2/v3, Telnet   |
| Diagnostics          | Management Address Conflict Detection, MAC Notification, Signal Contact, Device Status Indication, TCPDump, LEDs, Syslog, Persistent Logging on ACA, Port Monitoring with Auto-Disable, Link Flap Detection, Overload Detection, Duplex Mismatch Detection, Link Speed and Duplex Monitoring, RMON (1,2,3,9), Port Mirroring 1:1, Port Mirroring 8:1, Port Mirroring N:1, System Information, Self-Tests on Cold Start, SFP Management, Configuration Check Dialog, Switch Dump  |
| Configuration        | Automatic Configuration Undo (roll-back), Configuration Fingerprint, Text-based Configuration File (XML), BOOTP/DHCP Client with Auto-Configuration, DHCP Server: per Port, DHCP Server: Pools per VLAN, AutoConfiguration Adapter ACA21/22 (USB), HiDiscovery, Command Line Interface (CLI), CLI Scripting, Full-featured MIB Support, Context-sensitive Help   |
| Security             | MAC-based Port Security, Port-based Access Control with 802.1X, Guest/unauthenticated VLAN, Integrated Authentication Server (IAS), RADIUS VLAN Assignment, Denial-of-Service Prevention, Access to Management restricted by VLAN, Device Security Indication, Audit Trail, CLI Logging, HTTPS Certificate Management, Restricted Management Access, Appropriate Use Banner, Configurable Password Policy, Configurable Number of Login Attempts, SNMP Logging, Multiple Privilege Levels, Local User Management, Remote Authentication via RADIUS, User Account Locking                                 |
| Time synchronisation | Buffered Real Time Clock, SNTP Client, SNTP Server   |
| Miscellaneous        | Digital IO Management, Manual Cable Crossing, Port Power Down  |

#### Ambient conditions

|                                    |            |
|------------------------------------|------------|
| Operating temperature              | -40-+70 °C |
| Storage/transport temperature      | -40-+70 °C |
| Relative humidity (non-condensing) | 1- 95 %    |

## Mechanical construction

|                  |                         |
|------------------|-------------------------|
| Dimensions       | 73 mm x 138 mm x 115 mm |
| Weight           | 500                     |
| Housing          | Plastic                 |
| Mounting         | DIN Rail                |
| Protection class | IP30                    |

## Mechanical stability

|                         |  |
|-------------------------|--|
| IEC 60068-2-6 vibration | 5 Hz ... 8,4 Hz with 3,5 mm amplitude; 2 Hz ... 13,2 Hz with 1 mm amplitude; 8,4 Hz ... 200 Hz with 1 g; 13,2 Hz ... 100 Hz with 0,7 g |
| IEC 60068-2-27 shock    | 15 g, 11 ms duration   |

## EMC interference immunity

|                                      |   |
|--------------------------------------|---|
| EN 61000-4-2 electrostatic discharge | 6 kV contact discharge, 8 kV air discharge                          |
| EN 61000-4-3 electromagnetic field   | 10 V/m (80-2000 MHz); 5 V/m (2000-2700 MHz); 3 V/m (5100-6000 MHz)  |
| EN 61000-4-4 fast transients (burst) | 2 kV power line, 2 kV data line                                     |
| EN 61000-4-5 surge voltage           | power line: 2 kV (line/earth) and 1 kV (line/line); data line: 2 kV |
| EN 61000-4-6 conducted immunity      | 10 V (150 kHz-80 MHz)   |

## EMC emitted immunity

|                   |                            |
|-------------------|----------------------------|
| EN 55022          | EN 55032 Class A           |
| FCC CFR47 Part 15 | FCC 47CFR Part 15, Class A |

## Approvals

|  |                             |
|--|-----------------------------|
| Basis Standard                         | CE, FCC, EN61131, EN62368-1 |
| Safety of industrial control equipment | cUL61010                    |

## Scope of delivery and accessories

|                   |  |
|-------------------|--|
| Accessories       | AutoConfiguration Adapter ACA22-USB-C (EEC) 942239001; 6-pin terminal block with screw lock (50 pieces) 943 845-013; 2-pin terminal block with screw lock (50 pieces) 943 845-009; Industrial HiVision Network Management Software 943 156-xxx |
| Scope of delivery | 1 × Device 1 × General safety instructions 1 × Terminal block for supply voltage and signal contact; 1 × Terminal block for the digital input  |

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.