

100pcs 3:1 Heat shrink adhesive lined tube-assortment

Item No. : 1905CA061

This range is particularly suitable for hobbyists, craftsmen, field service, service workshops, electronics and the laboratory needs.

100 pieces of shrinking ration 3:1 standard shrinking tube for a range of application diameter from 1.6 to 12.7 mm.


Hot-melt adhesive lined tubing in the Black and White color.

The heat-shrink tubing can be used for insulation, protective covering of components, as anti-kink protection, protection against corrosion, as well as repair of cables and lines, and much more be used.



Shrinking ratio	3 : 1
Material	PE
Shrinking temperature	90°C - 125°C
Operation temperature	-45°C - 125°C
Flammability	VW-1
Tensile strength	≥ 10.3Mpa
Elongation at break	≥ 300%
Rated voltage	600V
Dielectric strength	≥ 1.5kV/mm at 30sec
Volume resistivity	≥ 10 ¹⁴ Ω

set contents



Section	Heat shrink tube		Length	Color	pcs
	Inner diameter Ø	after shrink Ø			
1-1	1.6 mm	0.5 mm	32 mm	Black	13
1-2	1.6 mm	0.5 mm	32 mm	White	13
2-1	2.4 mm	0.8 mm	32 mm	Black	10
2-2	2.4 mm	0.8 mm	32 mm	White	10
3-1	3.2 mm	1.0 mm	32 mm	Black	10
3-2	3.2 mm	1.0 mm	32 mm	White	10
4-1	4.8 mm	1.6 mm	65 mm	Black	6
4-2	4.8 mm	1.6 mm	65 mm	White	6
5-1	6.4 mm	2.2 mm	65 mm	Black	4
5-2	6.4 mm	2.2 mm	65 mm	White	4
6-1	7.9 mm	2.7 mm	65 mm	Black	2
6-2	7.9 mm	2.7 mm	65 mm	White	2
7-1	9.5 mm	3.2 mm	95 mm	Black	2
7-2	9.5 mm	3.2 mm	95 mm	White	2
8-1	12.7 mm	4.2 mm	95 mm	Black	3
8-2	12.7 mm	4.2 mm	95 mm	White	3