

Constant Current LED Power Supply

SLT50-1050IL-E(800mA,900mA,950mA,1050mA)



Product description:

With slim profile of 21mm height, this type of power supply is exclusively designed for linear LED light fixture. The outline of SLT50-1050IL-E keeps same as ballast for easy installation in LED luminaire which replaces traditional fluorescent lamp. Dipswitch leads variety output current. Reliability ensures 50,000hrs working lifetime.



Standards:

EN61347-1
EN61347-2-13
EN61547
EN55015
EN61000-3-2
EN61000-3-3
EN62384
EN62493


Characteristics:

- Slim design with 21mm height
- Metal house class I power supply for constant current LED lamp.
- Quick connection terminal for wire cross selection 0.5-0.75mm²
- Open circuit , short circuit , over load and over temperature protection
- Auto restart after fault conditions removal
- SELV output(<60V)
- Surge protection voltage 2 kV (L to N),4 kV (L/N to earth)
- Efficiency:89% (AC230V , full load)


Specifications :

Model	SLT50-1050IL-E(800mA,900mA,950mA,1050mA)				
Output	turn on time(S)	≤0.5	≤0.5	≤0.5	≤0.5
	output current(mA)	800	900	950	1050
	output current tolerance ^①	+/-8%	+/-8%	+/-8%	+/-8%
	ripple current(mA)	480(lp-p)	550(lp-p)	600(lp-p)	700(lp-p)
	working voltage range(V)	27-54	27-54	27-54	27-54
	Max. output voltage(V)	59	59	59	59
	dimming interface	No			
	dimming range	n/a			
Input	rated supply voltage(Vac)	220-240	220-240	220-240	220-240
	voltage range(Vac)	198-264	198-264	198-264	198-264
	line frequency(Hz)	50/60	50/60	50/60	50/60
	input current(mA)	260	290	300	320
	efficiency ^②	89.0%	89.0%	89.0%	89.0%
	power factor ^②	0.95	0.95	0.95	0.95
	inrush current(Ipk)	11A/30us	11A/30us	11A/30us	11A/30us
Protection	over voltage protection	YES	YES	YES	YES
	short circuit protection	YES	YES	YES	YES
	over temperature protection	YES	YES	YES	YES
	automatic restart	YES	YES	YES	YES
	over load protection	YES	YES	YES	YES
	surge capacity	L-N: 2KV,L,N-PE: 4KV	L-N: 2KV,L,N-PE: 4KV	L-N: 2KV,L,N-PE: 4KV	L-N: 2KV,L,N-PE: 4KV
Ambient and Life	Ta(°C)	-20...50			
	Tc max. (°C)	85			
	Storage Temperature(°C)	-30...80			
	ambient humidity range	5%...85%RH, Not condensing			
	nominal life-time(hrs)	50'000@Tc=85°C			
Other	weight(g)	213			
	dimensions (LxWxH)(mm)	278x30x21			
	casing material	metal			
	housing colour	White			
	type of protection	IP20			
	protection class	CLASS I			
Note	<p>1.Tolerance : includes set up tolerance, line regulation and load regulation. 2.Tested at full load,230Vac.Refer to"Power Factor" and "EFFICIENT"curve graphs. 3.All parameters NOT specially mentioned are measured at nominal voltage input, rated load and 25 of ambient temperature. 4.The power supply is considered as a component that will be operated in combination with final equipment. Since EMC performance will be affected by the complete installation, the final equipment manufacturers must re-qualify EMC Directive on the complete installation again.</p>				


Dimensions(mm):



Wiring diagram:



Electrical curves:



note
For constant current power supply,"LOAD" means the percentage of the maximum rated output voltage.
For constant voltage power supply,"LOAD" means the percentage of the maximum rated output current.

Sales & Technical Support:

Self Electronics Co.,Ltd.

Add: No. 1345 Ju Xian Road, Ningbo Hi Tech Park, Ningbo, China

Tel: 0086-574-28805765,28805658(For English Assistance)

0086-574-28805678 (For Chinese Assistance)

Fax: 0086-574-28805656

E-mail: sales@self-ecg.com

<http://www.self-ecg.com>

Self Electronics Co.,Ltd.,Shenzhen Office

Add: Room2007,Xinglang Xuan,Xinghe Mingju,Fuming Road,Futian District,Shenzhen

Tel: 0086-755-83558850, 83558851

Fax: 0086-755-83558840

SELF ELECTRONICS GERMANY GMBH

Add:August-Horch-Str. 7,51149 Koeln

Tel: 0049 2203 18501-0

Fax: 0049 2203 18501-199

E-mail: saleseu@self-electronics.com

*Due to continuous improvements and innovations,specifications are subjected to change without notice.