

RT Pico



WX

RT Micro



WX



WT

RT Ultra



WX



| | Soldering Iron: WXPP ○ / WXPP MS ● | | | Soldering Iron: WXMP ○ / WXMP MS ● / WMRP ○ / WMRP MS ● | | | Soldering Iron: WXUP MS ● | | |
|--|------------------------------------|--|-------------------|---|--|-------------------|---------------------------|--|-------------------|
| | article | | a / b (mm) (inch) | article | | a / b (mm) (inch) | article | | a / b (mm) (inch) |

Conical

| | | | |
|--------------------------------|--|-----|-------|
| RTP 001 C T0050103199 | | 0.1 | 0.004 |
| RTP 001 C MS T0050107399 | | 0.1 | 0.004 |
| RTP 001 C NW T0050103299 | | 0.1 | 0.004 |
| RTP 001 C MS NW T0050101499 | | 0.1 | 0.004 |
| RTP 002 C T0050103399 | | 0.2 | 0.008 |
| RTP 002 C MS T0050101599 | | 0.2 | 0.008 |
| RTP 004 C T0050103499 | | 0.4 | 0.016 |
| RTP 004 C MS T0050101699 | | 0.4 | 0.016 |
| RTP 001 C X T0050103599 | | 0.1 | 0.004 |
| RTP 001 C X MS T0050101799 | | 0.1 | 0.004 |
| RTP 002 C X T0050103699 | | 0.2 | 0.008 |
| RTP 002 C X MS T0050101899 | | 0.2 | 0.008 |

| | | | |
|---------------------------------|--|-----|-------|
| RTM 001 C NW T005446299N | | 0.1 | 0.004 |
| RTM 001 C NW MS T0054462571N | | 0.1 | 0.004 |
| RTM 002 C T0054460199N | | 0.2 | 0.008 |
| RTM 002 C MS T0054461499N | | 0.2 | 0.008 |
| RTM 002 C L T0050100099 | | 0.2 | 0.008 |
| RTM 002 C L MS T0050100199 | | 0.2 | 0.008 |
| RTM 004 C X MS T0054463399N | | 0.4 | 0.016 |
| RTM 005 C X MS T0054463299N | | 0.5 | 0.019 |
| RTM 008 C T0054460299N | | 0.8 | 0.031 |
| RTM 008 C MS T0054461799N | | 0.8 | 0.031 |

| | | | |
|-------------------------------|--|-----|-------|
| RTU 004 C MS T0050104999 | | 0.4 | 0.016 |
| RTU 008 C MS T0050105099 | | 0.8 | 0.031 |
| RTU 016 C MS T0050105199 | | 1.6 | 0.063 |
| RTU 004 C X MS T0050105299 | | 0.4 | 0.016 |
| RTU 008 C X MS T0050105399 | | 0.8 | 0.031 |
| RTU 016 C X MS T0050105499 | | 1.6 | 0.063 |

Bevel Cut

| | | | |
|-----------------------------|--|-----|-------|
| RTP 004 B T0050103799 | | 0.4 | 0.016 |
| RTP 004 B MS T0050101999 | | 0.4 | 0.016 |
| RTP 012 B T0050103899 | | 1.2 | 0.047 |
| RTP 012 B MS T0050102099 | | 1.2 | 0.047 |

| | | | |
|------------------------------|--|-----|-------|
| RTM 004 B T0050100299 | | 0.4 | 0.016 |
| RTM 004 B MS T0050100399 | | 0.4 | 0.016 |
| RTM 012 B T0054460699N | | 1.2 | 0.047 |
| RTM 012 B MS T0054461799N | | 1.2 | 0.047 |

| | | | |
|-----------------------------|--|-----|-------|
| RTU 020 B MS T0050105599 | | 2.0 | 0.079 |
| RTU 035 B MS T0050105699 | | 3.5 | 0.138 |
| RTU 050 B MS T0050105799 | | 5.0 | 0.197 |


Chisel

| | | | |
|--------------------------------|--|-----------|---------------|
| RTP 002 S T0050103999 | | 0.2 / 0.1 | 0.008 / 0.004 |
| RTP 002 S MS T0050102199 | | 0.2 / 0.1 | 0.008 / 0.004 |
| RTP 002 S NW T0050104099 | | 0.2 / 0.1 | 0.008 / 0.004 |
| RTP 002 S NW MS T0050102299 | | 0.2 / 0.1 | 0.008 / 0.004 |
| RTP 004 S T0050104199 | | 0.4 / 0.2 | 0.016 / 0.008 |
| RTP 004 S MS T0050102399 | | 0.4 / 0.2 | 0.016 / 0.008 |
| RTP 008 S T0050104299 | | 0.8 / 0.3 | 0.031 / 0.012 |
| RTP 008 S MS T0050102499 | | 0.8 / 0.3 | 0.031 / 0.012 |
| RTP 010 S T0050104399 | | 1.0 / 0.3 | 0.039 / 0.012 |
| RTP 010 S MS T0050102599 | | 1.0 / 0.3 | 0.039 / 0.012 |
| RTP 013 S T0050104499 | | 1.3 / 0.3 | 0.051 / 0.012 |
| RTP 013 S MS T0050102699 | | 1.3 / 0.3 | 0.051 / 0.012 |

| | | | |
|---------------------------------|--|------------|---------------|
| RTM 003 S NW T0054462699N | | 0.3 / 0.1 | 0.012 / 0.004 |
| RTM 003 S NW MS T0054462671N | | 0.3 / 0.1 | 0.012 / 0.004 |
| RTM 004 S T0054461299N | | 0.4 / 0.15 | 0.016 / 0.006 |
| RTM 004 S MS T0054461599N | | 0.4 / 0.15 | 0.016 / 0.006 |
| RTM 006 S MS T0050100499 | | 0.6 / 0.4 | 0.024 / 0.016 |
| RTM 008 S T0054460999N | | 0.8 / 0.4 | 0.031 / 0.016 |
| RTM 008 S MS T0054462399N | | 0.8 / 0.4 | 0.031 / 0.016 |
| RTM 008 S X T0054460599N | | 0.8 / 0.4 | 0.031 / 0.016 |
| RTM 008 S X MS T0054461999N | | 0.8 / 0.4 | 0.031 / 0.016 |
| RTM 010 S T0050100599 | | 1.0 / 0.3 | 0.039 / 0.012 |
| RTM 010 S MS T0050100699 | | 1.0 / 0.3 | 0.039 / 0.012 |
| RTM 013 S T0054460399N | | 1.3 / 0.4 | 0.051 / 0.016 |
| RTM 013 S MS T0054461699N | | 1.3 / 0.4 | 0.051 / 0.016 |
| RTM 013 S X MS T0054460373N | | 1.3 / 0.5 | 0.051 / 0.019 |
| RTM 015 S T0054460499N | | 1.5 / 0.4 | 0.059 / 0.016 |
| RTM 015 S MS T0054461899N | | 1.5 / 0.4 | 0.059 / 0.016 |
| RTM 018 S T0050100799 | | 1.8 / 0.4 | 0.071 / 0.016 |
| RTM 018 S MS T0050100899 | | 1.8 / 0.4 | 0.071 / 0.016 |
| RTM 022 S T0054460899N | | 2.2 / 0.4 | 0.087 / 0.016 |
| RTM 022 S MS T0054462299N | | 2.2 / 0.4 | 0.087 / 0.016 |
| RTM 032 S T0050100999 | | 3.2 / 0.9 | 0.126 / 0.035 |
| RTM 032 S MS T0050101099 | | 3.2 / 0.9 | 0.126 / 0.035 |
| RTM 036 S T0054461999N | | 3.6 / 0.9 | 0.141 / 0.035 |
| RTM 036 S MS T0054463199N | | 3.6 / 0.9 | 0.141 / 0.035 |

| | | | |
|-------------------------------|--|-----------|---------------|
| RTU 015 S MS T0050105899 | | 1.5 / 0.4 | 0.059 / 0.016 |
| RTU 022 S MS T0050105999 | | 2.2 / 0.6 | 0.087 / 0.024 |
| RTU 032 S MS T0050106099 | | 3.2 / 0.8 | 0.126 / 0.031 |
| RTU 032 S L MS T0050106199 | | 3.2 / 0.8 | 0.126 / 0.031 |
| RTU 050 S MS T0050106299 | | 5.0 / 1.2 | 0.197 / 0.047 |
| RTU 076 S MS T0050106399 | | 7.6 / 1.5 | 0.299 / 0.059 |
| RTU 093 S MS T0050106499 | | 9.3 / 2.0 | 0.366 / 0.079 |

NO COMPROMISE.
PRECISION. PERFORMANCE. POWER.
EXPLORE THE NEW ACTIVE SOLDERING TIP RANGE



Knife

| | | | |
|--------------------------------|--|-----|-------|
| RTP 010 K T0050104599 | | 1.0 | 0.039 |
| RTP 010 K MS T0050102799 | | 1.0 | 0.039 |
| RTP 010 K NW T0050104699 | | 1.0 | 0.039 |
| RTP 010 K MS NW T0050102899 | | 1.0 | 0.039 |
| RTP 025 K T0050104799 | | 2.5 | 0.098 |
| RTP 025 K MS T0050102999 | | 2.5 | 0.098 |

| | | | |
|------------------------------|--|-----|-------|
| RTM 025 K T0050101199 | | 2.5 | 0.098 |
| RTM 025 K MS T0050101299 | | 2.5 | 0.098 |
| RTM 030 K T0054460799N | | 3.0 | 0.118 |
| RTM 030 K MS T0054462199N | | 3.0 | 0.118 |

Gullwing

| | | | |
|-----------------------------|--|-----|-------|
| RTP 020 G T0050104899 | | 2.0 | 0.079 |
| RTP 020 G MS T0050103099 | | 2.0 | 0.079 |

| | | | |
|------------------------------|--|-----|-------|
| RTM 020 G T0054461899N | | 2.0 | 0.079 |
| RTM 020 G MS T0054462499N | | 2.0 | 0.079 |

| | | | |
|-----------------------------|--|-----|-------|
| RTU 020 G MS T0050106599 | | 2.0 | 0.079 |
|-----------------------------|--|-----|-------|

- Standard tip
- Mil-Spec soldering tip
- not wettable

Measuring tip

| | | | |
|---------------------------|--|--|--|
| RTM 028 X T0054461399N | | | |
|---------------------------|--|--|--|

Blade

| | | | |
|-----------------------------|--|------|-------|
| RTU 100 K MS T0050106699 | | 10.0 | 0.393 |
| RTU 160 K MS T0050106799 | | 16.0 | 0.630 |
| RTU 200 K MS T0050106899 | | 20.0 | 0.078 |
| RTU 330 K MS T0050106999 | | 33.0 | 1.299 |

Weller®

www.weller-tools.com/nocompromise