

RT Pico



WX

RT Micro



WX



WT

RT Ultra



WX



	Soldering Iron: WXPP ○ / WXPP MS ●			Soldering Iron: WXMP ○ / WXMP MS ● / WMRP ○ / WMRP MS ●			Soldering Iron: WXUP MS ●		
	article		a / b (mm) (inch.)	article		a / b (mm) (inch.)	article		a / b (mm) (inch.)

### Conical

RTP 001 C RTP 001 C MS		0.1 0.004
RTP 001 C NW RTP 001 C NW MS		0.1 0.004 ●
RTP 002 C RTP 002 C MS		0.2 0.008
RTP 004 C RTP 004 C MS		0.4 0.016
RTP 001 C X RTP 001 C X MS		0.1 0.004
RTP 002 C X RTP 002 C X MS		0.2 0.008

RTM 001 C NW RTM 001 C NW MS		0.1 0.004 ●
RTM 002 C RTM 002 C MS		0.2 0.008
RTM 002 C L RTM 002 C L MS		0.2 0.008
RTM 004 C X MS		0.4 0.016
RTM 005 C X MS		0.5 0.019
RTM 008 C RTM 008 C MS		0.8 0.031

RTU 004 C MS		0.4 0.016
RTU 008 C MS		0.8 0.031
RTU 016 C MS		1.6 0.063
RTU 004 C X MS		0.4 0.016
RTU 008 C X MS		0.8 0.031
RTU 016 C X MS		1.6 0.063

### Bevel Cut

RTP 004 B RTP 004 B MS		0.4 0.016
RTP 012 B RTP 012 B MS		1.2 0.047

RTM 004 B RTM 004 B MS		0.4 0.016
RTM 012 B RTM 012 B MS		1.2 0.047

RTU 020 B MS		2.0 0.079
RTU 035 B MS		3.5 0.138
RTU 050 B MS		5.0 0.197

### Chisel

RTP 002 S RTP 002 S MS		0.2 / 0.1 0.008 / 0.004
RTP 002 S NW RTP 002 S NW MS		0.2 / 0.1 0.008 / 0.004 ●
RTP 004 S RTP 004 S MS		0.4 / 0.2 0.016 / 0.008
RTP 008 S RTP 008 S MS		0.8 / 0.3 0.031 / 0.012
RTP 010 S RTP 010 S MS		1.0 / 0.3 0.039 / 0.012
RTP 013 S RTP 013 S MS		1.3 / 0.3 0.051 / 0.012

RTM 003 S RTM 003 S MS		0.3 / 0.15 0.012 / 0.006
RTM 003 S NW RTM 003 S NW MS		0.3 / 0.1 0.012 / 0.004 ●
RTM 004 S MS		0.4 / 0.2 0.016 / 0.008
RTM 006 S MS		0.6 / 0.4 0.024 / 0.016
RTM 008 S RTM 008 S MS		0.8 / 0.4 0.031 / 0.016
RTM 008 S X RTM 008 S X MS		0.8 / 0.4 0.031 / 0.016
RTM 010 S RTM 010 S MS		1.0 / 0.3 0.039 / 0.012
RTM 013 S RTM 013 S MS		1.3 / 0.4 0.051 / 0.016
RTM 013 S X RTM 013 S X MS		1.3 / 0.5 0.051 / 0.019
RTM 015 S RTM 015 S MS		1.5 / 0.4 0.059 / 0.016
RTM 018 S RTM 018 S MS		1.8 / 0.4 0.071 / 0.016
RTM 022 S RTM 022 S MS		2.2 / 0.4 0.087 / 0.016
RTM 032 S RTM 032 S MS		3.2 / 0.9 0.126 / 0.035
RTM 036 S RTM 036 S MS		3.6 / 0.9 0.141 / 0.035

RTU 015 S MS		1.5 / 0.4 0.059 / 0.016
RTU 022 S MS		2.2 / 0.6 0.087 / 0.024
RTU 032 S MS		3.2 / 0.8 0.126 / 0.031
RTU 032 S L MS		3.2 / 0.8 0.126 / 0.031
RTU 050 S MS		5.0 / 1.2 0.197 / 0.047
RTU 076 S MS		7.6 / 1.5 0.299 / 0.059
RTU 093 S MS		9.3 / 2.0 0.366 / 0.079

**NO COMPROMISE.**  
PRECISION. PERFORMANCE. POWER.  
EXPLORE THE NEW ACTIVE SOLDERING TIP RANGE

### Knife

RTP 010 K RTP 010 K MS		1.0 0.039
RTP 010 K NW RTP 010 K NW MS		1.0 0.039 ●
RTP 025 K RTP 025 K MS		2.5 0.098

RTM 025 K RTM 025 K MS		2.5 0.098
RTM 022 K RTM 022 K MS		2.2 0.087
RTM 030 K RTM 030 K MS		3.0 0.118

### Gullwing

RTP 020 G RTP 020 G MS		2.0 0.079
---------------------------	--	--------------

RTM 020 G RTM 020 G MS		2.0 0.079
---------------------------	--	--------------

RTU 020 G MS		2.0 0.079
--------------	--	--------------

RT Pico 40 watts    RT Micro 40 watts    RT Ultra 150 watts

- Standard tip
- Mil-Spec soldering tip
- not wettable

### Measuring tip

RTM Measuring tip ○

### Blade

RTU 100 K MS		10.0 0.393
RTU 160 K MS		16.0 0.630
RTU 200 K MS		20.0 0.078
RTU 330 K MS		33.0 1.299

**Weller**®

www.weller-tools.com/nocompromise