



# VOLTCRAFT®

## VOLTCRAFT® - TOP PERFORMANCE IN EVERY WAY

“Since 1982, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft’s success.”

## BS-14 MM / 25 M

# INSPECTION CAMERA WITH FIBER OPTIC CABLE AND REEL

CE  
VERSION 12/21

N° 2183202

This product is designed for optical troubleshooting or inspecting long pipe systems as well as machines and installations that are disconnected from a power supply. The flexible camera neck allows the camera on top to access inaccessible positions. The plastic camera cover protects the metal camera head from accidental contact with live parts.

The reel included with the product enables the camera and the camera neck to be rolled up easily, and the tripod ensures that the camera stands in a secure position. The 8 LEDs built into the camera head allow recording in completely dark areas. The brightness can be gradually adjusted using the connected endoscope. The waterproof camera neck and camera head are designed for contact with liquids (no acids or alkaline solutions). Power is supplied via the connected endoscope device.

### FEATURES:

Camera diameter 14 mm // Designed for VOLTCRAFT® endoscope BS-1500T // With spool and holder // Highly flexible and watertight (IP67) // CMOS sensor // Resolution 640 x 480 Pixels // 8 high-performance LEDs //

### TECHNICAL DATA:

Designed for	BS-1500 endoscope – item no. 1340787
Camera-Ø	14 mm
Adapter cable length	2 m (extended), 60 cm (coiled)
Image sensor	CMOS
Depth of field	5 - 60 cm
Resolution	640 x 480 Pixels
White balance	Automatic
Exposure	Automatic
Illuminant	8 LEDs (white)
Illuminance	max. 3000 lx (at a distance of 20 mm)
Min. bending radius	>10 cm
Protection type	IP67 (camera, camera neck waterproof)
Operating conditions	-20 to +60 °C, max. 95 % RH (non-condensing)
Storage conditions	-20 to +60 °C, max. 95 % RH (non-condensing)
Camera neck length	18 m
Push cable length	25 m
Dimensions (W x H x D)	approx. 45 x 45 x 25.5 cm
Weight	approx. 5.3 kg



### PACKAGE CONTENTS:

Camera with 25 m cable and reel // Holder with 1 x screw and 2 x spacer washers // 1x adapter cable (5 pin to 8 pin) // 1 x camera cover // Operating instructions //

This data sheet is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represent the technical status at the time of printing.

© Copyright 2022 by Conrad Electronic SE.

2183202\_V2\_1221\_01\_PIX\_ds