



SIMPLE MANUAL

Micro Hi-Fi Audio

To view the instructions of advanced features,
visit <http://www.lg.com> and then download Owner's Manual.
Some of the content in this manual may differ from your unit.

MODEL
CM2460DAB



MFL71379811
1908_Rev01

www.lg.com

Copyright © 2019 LG Electronics Inc. All Rights Reserved.

ENGLISH

DEUTSCH

FRANÇAIS

NEDERLANDS

SLOVENŠČINA

ITALIANO


ESPAÑOL

EAHHNIKA

PORTUGUÊS




Front Panel



- 1** (Power)
Switches the unit ON or OFF.
- 2** **F**
Selects the function or input source.
- 3** (Skip/Search)
- Searches backward or forward.
- Skips to the previous/next track/file.
- TUNING - / +**
- Selects the radio stations.
- Scans DAB+ stations by pressing and holding.
- 4** (Play/Pause)
- Starts or pauses playback.
- Selects Stereo/Mono.
- 5**
Opens or closes the disc tray.
- 6** Remote sensor
- 7** Display window
- 8** Volume Knob
Adjusts volume of speaker.
- 9** USB
Plays the audio files by connecting the USB device.
- 10** Disc tray
- 11** **PORT. IN**
Connects to a Portable device.

Rear Panel



- 1** **DAB+/FM ANTENNA**
- 2** **SPEAKERS (L/R)** terminals
- 3** **POWER IN**

Controller App




Download the **Music Flow Bluetooth** App to your device.

LG Sound Sync (Wireless)



For more information, download the online owner's manual. <http://www.lg.com>


Speaker Connection



How to disconnect the wireless network connection or the wireless device

Turn off the unit by pressing the power button for more than 5 seconds.

Replacement of battery



Declaration of Conformity



Hereby, LG Electronics declares that the radio equipment type MICRO HI-FI SYSTEM is in compliance with Directive 2014/53/EU. The full text of the EU declaration of conformity is available at the following internet address:

<http://www.lg.com/global/support/cedoc/cedoc#>

For consideration of the user, this device should be installed and operated with a minimum distance of 20 cm between the device and the body.

Frequency range	Output power (Max.)
2402 to 2480 MHz	10 dBm

Additional Information

Specifications

Power Requirements	Refer to the main label on the unit.
Power Consumption	Refer to the main label on the unit. Networked standby : 0.5 W (If all network ports are activated.)
Dimensions (W x H x D)	Approx. 230 mm x 126 mm x 253 mm
Bus Power Supply (USB)	5 V 500 mA
Amplifier (Total RMS output power)	100 W

Design and specifications are subject to change without notice.

