



REVISION RECORD				1
REV	ECN	DESCRIPTION	DRFT	DATE



1. Pollution Degree	2
Overvoltage Category	III
Rate Impulse Voltage(KV)	14.0KV
Rate Voltage(V)	250V
Rate Current(A)	15A

- IEC Standard
1. Rated voltage/current : 300V / 10A
 2. Withstanding voltage : AC1600V/1Min.
 3. Torque value : M2.5 , 3.54lb.in
 4. Wire range : 28~12AWG

- UL Standard
1. Torque value : M2.5 , 0.4N•m
 3. Wire range : 2.5mm²

- NOTES:
- 1.Dimension shall be interpreted per ASME Y14.5-2009
 - 2.Pitch : 5.08mm, Poles : N=02~12P
 - 3.Stripping length : 7~8mm
 - 4.Operating temperature: -40°C~+105°C
 - 5.Undimensioned tolerances:

Pitch range in mm		Nominal dimension range in mm							
Over	Over	Over	Over	Over	Over	Over	Over	0.1/10	0.1/10
6	10	30	60	100	150				
TO	TO	TO	TO	TO	TO				
6	10	24	30	60	100	150			

6. RoHS Compliance

2EDGKHM - 5.08 - XXP - 1Y - 00A (H)
(Series No.) (Pitch) (Poles) (Single Pitch)
(RoHS)
00A-(Standard)

(Color): 1.(Grey) 2.(Blue) 3.(Black) 4.(Green) 5.(Orange)
6.(Red) 7.(Transparent) 8.(Yellow) 9.(White)

DETACHED LISTS		THIRD ANGLE PROJECTION	
PART NO.:	/	DRFT:	/
APPD:	/	DRFT:	/
CHOD:	/	DRFT:	/
NAME:	2EDGKHM-5.08-XXP-1Y-00A(H)	TITLE:	CUSTOMER DRAWING
DRAWING NO.:	/	REV	DO
SCALE	1:1	SHEET	1/1

DEGSON 宁波德森电子有限公司
NINGBO DEGSON ELECTRICAL CO.,LTD

2EDGKHM-5.08-XXP-1Y-00A(H)

CUSTOMER DRAWING

DRAWING NO.:



THIRD ANGLE PROJECTION

DO NOT SCALE

SCALE

1:1