


No. 2203110 // YH-125X65 // 125 x 65 mm



Isc: Output current at 0 loading, it is the short circuit current. The output power is zero.

Voc: Output voltage at starting loading. It is the starting voltage. The output power is zero.

Along with the changing of the loading of this item, working point and output power will change continually.

As it reaches to the max point, the output current and voltage will be the max working voltage (V_m), and max working current (I_m).

Technical data

| | |
|-----------------------------|--|
| V_m | 9 V |
| I_m | 109 mA |
| Dimension | 125 x 65 mm (length/width tolerance ± 0.2 mm; thickness tolerance ± 0.5 mm) |
| Testing Condition | AM1.5; 25 °C; 1000 w/m ² |
| Operation Standard | GB/T 9535-1998 (e.g. IEC 61215: 1993) |
| Operation performance | Compare with suitable loading |
| Operation environment | Outdoors: -20 to +80 °C |