

REVISION RECORD

REV	ECN	DESCRIPTION	DRFT	DATE
-----	-----	-------------	------	------

NOTES1:

UL Standard

1.Rated voltage/current : 300V / 15A

2.Withstanding voltage : AC1600V/1Min.
IEC Standard

Pollution degree	2
Overvoltage category	III
Rate impulse voltage(KV)	4.0KV
Rate voltage(V)	320V
Rate current(A)	10A

NOTES2:

1.Dimension shall be interpreted per
ASME Y14.5-2009

2.Pitch : 5.0/5.08mm, Poles : N=4~48P


3.Operating temperature:-40°C~+105°C

4.Undimensioned tolerances:

Pitch range in mm		Nominal dimension range in mm		
Over 6 TO 10	Over 10 TO 24	Over 30 TO 60	Over 60 TO 100	Over 100 TO 150
±0.15	±0.20	±0.30	±0.50	±0.70
±0.30	±0.50	±0.70	±1.00	±1.30
±0.50	±0.70	±1.00	±1.30	±2*

5.RoHS Compliance

2EDGVTC - 5.0/5.08 - XXP - 1Y - 00A (H)
 (Series No.) (Pitch) (Poles) (Single Pitch) (Color):1.(Grey)
 2.(Blue)
 3.(Black)
 4.(Green)
 5.(Orange)
 6.(Red)
 7.(Transparent)
 8.(Yellow)
 9.(White)

DETACHED LISTS	PART NO.:	 宁波高松电子有限公司 NINGBO DEGSON ELECTRICAL CO., LTD			
	APPD:	NAME: 2EDGVTC-5.0/5.08-XXP-1Y-00A(H)			
	CHKD:	TITLE: CUSTOMER DRAWING			
	DRFT:	REV: /			
 THIRD ANGLE PROJECTION	DRAWING NO.:		SHEET		DO
	 MM (INCH)		SCALE		1:1

