

REVISION RECORD

REV	ECN	DESCRIPTION	DRFT	DATE
-----	-----	-------------	------	------

NOTES1:

UL Standard

- 1.Rated voltage/current : 300V / 8A
- 2.Withstanding voltage : AC1600V/1Min.
- 3.Torque value : M2 , 1.77Lb.in
- 4.Wire range : 28~16AWG

IEC Standard

1.	Pollution degree	2
	Overvoltage category	II
	Rate impulse voltage(KV)	4.0KV
	Rate voltage(V)	450V
	Rate current(A)	7A

2.Torque value : M2 , 0.2N·m

3.Wire range : 0.5~1.5mm²

NOTES2:






- 1.Dimension shall be interpreted per ASME Y14.5-2009
- 2.Pitch : 5.08mm, Poles : N=02~12P
- 3.Stripping length : 6~7mm
- 4.Operating temperature:-40°C~+105°C
- 5.Undimensioned tolerances:

Pitch range in mm		Nominal dimension range in mm		
Over 6 TO 10	Over 10 TO 24	Over 30 TO 60	Over 60 TO 100	Over 100 TO 150
±0.15	±0.20	±0.30	±0.50	±0.70
±0.20	±0.30	±0.30	±0.50	±0.70
±0.30	±0.50	±0.70	±1.00	±1.30
±0.50	±0.70	±1.00	±1.30	±2.0

6.RoHS Compliance

15EDGKM - 5.08 - XXP - 1Y - 00A (H)
(Series No.) (Pitch) (Poles) (Single Pitch) (Color)
00A-(Standard) (RoHS)

(Color):1.(Grey)2.(Blue)3.(Black)4.(Green)5.(Orange)
6.(Red)7.(Transparent)8.(Yellow)9.(White)



DETACHED LISTS	PART NO.:	NINGBO DEGSON ELECTRONICS CO., LTD			
	APPD:	NAME: 15EDGKM-5.08-XXP-1Y-00A(H)			
	CHKD:	TITLE: CUSTOMER DRAWING			
	DRFT:	DRAWING NO.:		REV	DO
	THIRD ANGLE PROJECTION		MM (INCH)	SHEET	1/1

DO NOT SCALE DRAWING

SCALE

1:1