

REVISION RECORD

REV	ECN	DESCRIPTION	DRFT	DATE
-----	-----	-------------	------	------

NOTES1:

UL Standard

1.Rated voltage/current : 300V / 15A

2.Withstanding voltage : AC1600V/1Min.

IEC Standard

Pollution degree	2
Overvoltage category	III
Rate impulse voltage(KV)	4.0KV
Rate voltage(V)	320V
Rate current(A)	10A

NOTES2:

1.Dimension shall be interpreted per ASME Y14.5-2009

2.Pitch : 5.0/5.08mm, Poles : N=4~48P

3.Operating temperature: -40°C~+105°C

4.Undimensioned tolerances:






Pitch range in mm		Nominal dimension range in mm		
Over 6	Over 10	Over 30	Over 60	Over 100
TO 6	TO 24	TO 60	TO 100	TO 150
±0.15	±0.20	±0.30	±0.50	±1.00
±0.20	±0.30	±0.50	±0.70	±1.30
±0.30	±0.50	±0.70	±1.00	±1.30
±0.50	±0.70	±1.00	±1.30	±2.0

5.RoHS Compliance

2EDGRT - 5.0/5.08 - XXP - 1Y - 00A (H)

(Series No.) (Pitch) (Poles) (Single Pitch) (Color): 1.(Grey)
2.(Blue)
3.(Black)
4.(Green)
5.(Orange)
6.(Red)
7.(Transparent)
8.(Yellow)
9.(White)

(RoHS)
00A-(Standard)



DETACHED LISTS	PART NO.:	/				NINGBO DEGSON ELECTRICAL CO., LTD	
	APPD:	/		NAME:		2EDGRT-5.0/5.08-XXP-1Y-00A(H)	
	CHKD:	/		TITLE:		CUSTOMER DRAWING	REV
	DRFT:	/		DRAWING NO.:		/	DO
THIRD ANGLE PROJECTION		MM (INCH)		DO NOT SCALE DRAWING		SCALE	1:1