



## QC-71-1.0-2.5 AX<sub>2</sub>

I <sub>max</sub> (amps)	2,8 A	ΔT = ΔT <sub>max</sub> ; Th = 25°C ± 0.5 K
U <sub>max</sub> (volt)	8,1 V	ΔT = ΔT <sub>max</sub> ; Th = 25°C ± 0.5 K
ΔT <sub>max</sub> (kelvin)	-72°K	I = I <sub>max</sub> ; Th = 25°C ± 0.5 K; Q = 0 W
Q <sub>max</sub> (watts)	13,3 W	I = I <sub>max</sub> ; Th = 25°C ± 0.5 K; ΔT = 0 K
AC resistance (ohms)	2,7 Ω	25°C ± 0.5 K

Environment: dry air, N<sub>2</sub>  
 tolerances for thermal and electrical parameters ± 10%  
 dimensions in millimeters




OPTIONS: X1=A	T <sub>max</sub> =100°C
X1=M	T <sub>max</sub> =200°C; high cycle resistance
X1=MM	T <sub>max</sub> =200°C; double high cycle resistance
X2=none	none sealing
X2=S	silicone sealing
X2=X	epoxy sealing
other specials: please contact Quick-Ohm	

**cold side and hot side ceramics: Al<sub>2</sub>O<sub>3</sub>, white 96%**


# QC-71-1.0-2.5

Thot:  
**25°C**

cooling power  
↑




↑ module voltage




# QC-71-1.0-2.5

$T_{hot}$ :  
**50°C**

cooling power  
 ↑



module voltage



$R_{th} = 10,28 \text{ K/W}$

←  $\Delta T = T_{cold} - T_{hot}$