

REVISION RECORD					
REV	ECN	DESCRIPTION	DFT	DATE	

NOTES1:
UL Standard
1.Rated voltage/current : 300V / 15A
2.Withstanding voltage : AC1600V/1Min.
3.Torque value : M3 , 5.31lb.in
4.Wire range : 28~12AWG
IEC Standard

1. Pollution degree	2.	2.	3.
Overvoltage category	II	III	III
Rate impulse voltage(kV)	4.0kV	4.0kV	4.0kV
Rate voltage(V)	630V	320V	250V
Rate current(A)	12A		




2.Torque value : M3 , 0.6N·m
3.Wire range : 0.2~2.5mm²

NOTES2:

1.Dimension shall be interpreted per
ASME Y14.5-2009
2.Pitch : 5.08mm, Poles : N=02P~24P
3.Stripping length : 7~8mm
4.Operating temperature: -40°C~+105°C
5.Undimensioned tolerances:


Pitch range in mm		Nominal dimension range		
Over	10	Over	30	Over
To	60	To	100	150
6	10	TO	TO	150
10	24	30	60	100
±0.15/±0.20/±0.30/±0.30/±0.50/±0.70/±1.00/±1.30		±2°		

6.RoHS Compliance



2EDG - DKM - 5.08 - XXP - 1Y - 00A (H)
(Series No.) (Pitch) (Poles) (Single Pitch) (Color):1.(Grey)
2.(Blue)
3.(Black)
4.(Green)
5.(Orange)
6.(Red)
7.(Transparent)
8.(Yellow)
9.(White)

Poles	Q"Ty
2P~4P	1pcs
5P~9P	2pcs
10~24P	3pcs



DETACHED LISTS					
PART NO.:	/	NAME:	NINGBO DEGSON ELECTRICAL CO., LTD		
APPD:	/	CHKD:	2EDG-DKM-5.08-XXP-1Y-00A(H)		
DFT:	/	TITLE:	CUSTOMER DRAWING	REV	DO
THIRD ANGLE PROJECTION		DRAWING NO.:	/	SHEET	1/1
		THIRD ANGLE PROJECTION	DO NOT SCALE DRAWING	SCALE	1:1