

REVISION RECORD

REV	ECN	DESCRIPTION	DRFT	DATE
-----	-----	-------------	------	------

NOTES1:

UL Standard

- 1.Rated voltage/current : 300V / 15A
- 2.Withstanding voltage : AC1600V/1Min.
- 3.Torque value : M3 , 5.32Lb.in
- 4.Wire range : 28~12AWG

IEC Standard

1. Pollution degree	2	2	3
Overvoltage category	II	III	III
Rate impulse voltage(KV)	4.0K	4.0KV	4.0KV
Rate voltage(V)	630V	320V	250V
Rate current(A)	12A		

2.Torque value : M3 , 0.6N·m

3.Wire range : 0.2~2.5mm²

NOTES2:


- 1.Dimension shall be interpreted per ASME Y14.5-2009
- 2.Pitch : 5.08mm, Poles : N=02P~24P
- 3.Stripping length : 7~8mm
- 4.Operating temperature: -40°C~+105°C
- 5.Undimensioned tolerances:

Pitch range in mm			Nominal dimension range in mm					
To	Over	To	To	Over	Over	Over	Over	
6	6	10	30	30	60	100	150	0.1/10
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30	±2°





6.RoHS Compliance

2EDG - UDBM - 5.08 - XXP - 1Y - 00A (H)
(RoHS)
00A-(Standard)
(Color):1.(Grey)
2.(Blue)
3.(Black)
4.(Green)
5.(Orange)
6.(Red)
7.(Transparent)
8.(Yellow)
9.(White)

DETACHED LISTS	PART NO.:	/			宁波高松电子有限公司 NINGBO DEGSON ELECTRICAL CO., LTD		
	APPD:	/			NAME:		
	CHKD:	/			2EDG-UDBM-5.08-XXP-1Y-00A(H)		
	DRFT:	/			TITLE:	CUSTOMER DRAWING	REV
	THIRD ANGLE PROJECTION			DRAWING NO.:	/	SHEET	DO
			MM (INCH)	DO NOT SCALE DRAWING		SCALE	1:1



5.08X(N-1) 3.3
5.08 5.08



Poles	Q"TY
2P~4P	1pcs
5P~9P	2pcs
10~24P	3pcs

34.6

11.8

H
G
F
E
D
C
B
AH
G
F
E
D
C
B
A