



QC-32-0.6-1.2 X₁X₂

I _{max} (amps)	1,5 A	ΔT = ΔT _{max} ; Th = 25°C ± 0.5 K
U _{max} (volt)	3,7 V	ΔT = ΔT _{max} ; Th = 25°C ± 0.5 K
ΔT _{max} (kelvin)	-73°K	I = I _{max} ; Th = 25°C ± 0.5 K; Q = 0 W
Q _{max} (watts)	3,22 W	I = I _{max} ; Th = 25°C ± 0.5 K; ΔT = 0 K
AC resistance (ohms)	2,3 Ω	25°C ± 0.5 K

Environment: dry air, N₂
 tolerances for thermal and electrical parameters ± 10%
 dimensions in millimeters




X1=M	T _{max} =200°C; high cycle resistance
X1=MM	T _{max} =200°C; double high cycle resistance
X2=none	none sealing
X2=S	silicone sealing
X2=X	epoxy sealing
other specials: please contact Quick-Ohm	

cold side and hot side ceramics: Al₂O₃, white 96%


QC-32-0.6-1.2

Hot side temperature: **25°C**

↑ cooling power



↑ module voltage




QC-32-0.6-1.2


T_{hot}:
50°C

cooling power
↑

hot side temperature:



module voltage



R_{th} = 44,32 K/W

← ΔT = T_{cold} - T_{hot}