

KERN EOE 150K50L



Parcel scales with big platform for fast and easy weighing in the office, production, dispatch etc.



Service

Adjustment at the location of installation: 961-249

DAkkS Certificate: 963-129

Category

Brand: KERN

Category: Balances

Product Group: Platform scale

Packaging & shipping

Delivery: 24 h

Dimensions packaging (WxDxH): 660 x 600 x 90 mm

Gross weight: 15,300 kg

Net weight: 13,800 kg

Shipping method: Parcel service

Construction

Cable length of display device: 2,700 m

Casing material: plastic

Dimensions of display device (WxDxH): 235 x 114 x 51 mm

Dimensions of weighing plate (WxDxH): 550 x 550 x 58 mm

Material weighing plate: Steel lacquered

Wall mount: yes

Weighing surface (WxD): 550 x 550 mm

Piktogramme

STANDARD



OPTION



Measuring system

Adjustment options: External calibration

Linearity: 100 g

Readability [d]: 50 g

Recommended adjusting weight: 100 kg (M3)

Repeatability: 50 g

Resolution: 3000

Tare range: 150 kg

Warm up time: 10 min

Weighing capacity [Max]: 150 kg

Weighing system: Strain gauge

Weighing units: kg lb

Display

Display digit height: 2,500 cm

Functions

Data hold function: yes

Vibration-free weighing (Animal weighing program): yes

Environmental conditions

Maximum humidity: 80 %

Maximum operating temperature: 35 °C

Minimum ambient temperature: 5 °C

Power supply

Battery: 4x1.5 V AA

Input voltage: 220 V - 240 V AC 50 Hz

Mains adapter: Mains adapter external

Mains adapter/adaptor included: CH EURO UK US

Operating time: 100 h