

# Data sheet

## SSD 4-00 SAT twin antenna wall outlet 5...2200 MHz | CATV | SAT | SAT



- ✓ Twin terminal type
- ✓ Suitable for return path 5...65 MHz
- ✓ With cover plate and frame



### Technical data

Tap method	Filter circuit/directional coupler
<b>Trunk line</b>	
Frequency range input	5...2200 MHz
Frequency range input right	5...2200 MHz
Frequency range input left	5...2200 MHz
Isolation internal	≥ 20 dB
Suitable cables (Inner conductor   outer diameter)	0,63...1,13 mm   4,70...7,35 mm
<b>TV connector</b>	
Connector type	IEC-male
Frequency range	135...862 MHz   5...65MHz
Tap loss	≤ 2 dB   ≤ 2 dB
<b>Radio connector</b>	
Connector type	IEC-female
Frequency range	87...125 MHz
Tap loss	≤ 2 dB
<b>SAT connector left</b>	
Connector type	F-female
Frequency range	950...2200 MHz
Tap loss	≤ 2 dB
DC power pass to trunk	F-female
<b>SAT connector right</b>	
Connector type	yes
Frequency range	5...2200 MHz
Tap loss	≤ 2 dB
DC power pass to trunk	yes
<b>General</b>	
Dimensions (W × H × D) appr.	78 × 78 × 46 mm
Weight	0,149 kg