



QC-63-1.0-3.0 X₁X₂

I _{max} (amps)	3,5 A	ΔT = ΔT _{max} ; Th = 25°C ± 0.5 K
U _{max} (volt)	7,2 V	ΔT = ΔT _{max} ; Th = 25°C ± 0.5 K
ΔT _{max} (kelvin)	-72°K	I = I _{max} ; Th = 25°C ± 0.5 K; Q = 0 W
Q _{max} (watts)	14,8 W	I = I _{max} ; Th = 25°C ± 0.5 K; ΔT = 0 K
AC resistance (ohms)	1,9 Ω	25°C ± 0.5 K

Environment: dry air, N₂
 tolerances for thermal and electrical parameters ± 10%
 dimensions in millimeters




OPTIONS: X1=A	T _{max} =100°C
X1=M	T _{max} =200°C; high cycle resistance
X1=MM	T _{max} =200°C; double high cycle resistance
X2=none	none sealing
X2=S	silicone sealing
X2=X	epoxy sealing
other specials: please contact Quick-Ohm	

cold side and hot side ceramics: Al₂O₃, white 96%


QC-63-1.0-3.0

T_{hot}:
25°C

cooling power
↑



↑ module voltage




R_{th} = 8,89 K/W


QC-63-1.0-3.0

T_{hot} :
50°C

cooling power
↑



module voltage



$R_{th} = 9,28 \text{ K/W}$

← $\Delta T = T_{cold} - T_{hot}$