# Image: Second stateImage: Second stateAny-Grid™ Hybrid Inverter Charger



# phocos

143 mm

# **Technical Drawing**



# 468 mm

309 mm

## **Product Introduction**

The Phocos Any-Grid<sup>™</sup> PSW-H Inverter Charger Series (Pure Sine Wave Hybrid) represents Phocos' most versatile line of inverters/ chargers. Flexibility and reliability are key characteristics of this product line, with a strong potential for cost saving opportunities in real world conditions. The PSW-H converts DC (Direct Current) energy into AC (Alternating Current), with multiple advantages beyond standard inverters. This product includes an integrated MPPT charge controller and can function as an AC to DC battery charger, which provides flexible energy access solutions in a broad range of applications.

The battery can be charged from solar and/or an AC source (public grid or generator), with easily programmable priorities. It can function without an AC source or alternatively even without solar, as a pure uninterruptible power supply (UPS). When the utility grid or AC generator fails, the PSW-H immediately switches to 'Off-Grid' mode within 10 ms (typical, in UPS mode) to securely power the loads at all times. Solar can be set as the priority energy source to save electricity costs.

The Any-Grid<sup>™</sup> PSW-H can function in a battery-free mode. In this mode, for installations with stable public grids, grid energy consumption can be reduced without the need to invest in a costly battery bank. Additionally, power can be supplied directly to loads from the grid and solar simultaneously.

This unit comes with a quality, integrated MPPT charge controller. The controller accepts particularly high PV voltages, allowing many PV modules to be connected in series, decreasing installation cost and avoiding combiner boxes. Up to 9 inverters can be connected in parallel or 3-phase for up to 45 kW of synchronized AC power.

### **Product Features**

- Flexible, advanced features with options to solve many common challenges in the field
- Integrated high-voltage MPPT charge controller. The high-voltage PV connection means in most scenarios the PV modules can simply be connected in series, avoiding costly combiner boxes and string fuses or diodes, thus reducing total system cost
- Integrated AC battery charger
- Charge controller functions even if inverter is turned off to keep
  batteries fully charged
- Compatible with LiFePO4 (lithium iron phosphate) batteries
- Functions without an expensive battery to reduce energy consumption from the grid with minimal investment
- Detachable display / communication unit with 6 LEDs and an intuitive LCD screen
- High level of connectivity: BLE, USB-OTG (on-the-go), RS-485, RS-232, relay for generator start
- Datalogger with up to 60 days of data storage
- Store or load parameters via USB for quick configuration
- Integrated buzzer for error indications
- Galvanic isolation of battery allows positive or negative grounding
- Up to 9 inverters can be connected in parallel or 3-phase for up to 45 kW of synchronized AC power
- Removable filter reduces dust buildup in the inverter

# Image: Second stateImage: Second stateAny-Grid™ Hybrid Inverter Charger

	6	
ഫ	X	論

# phocos

### **Technical Data**

Туре	PSW-H-5KW-230/48V	
Output Waveform	Pure Sine Wave	
System Voltage	48 VDC	
Rated Power	5000 VA / 5000 W	
Max. Charge Current (PV)	80 A	
Max. Charge Current (AC)	80 A	
Max. Total Charge Current	80 A	
Float Charge	55.2 VDC (adjustable)	
Boost Charge	57.6 VDC (adjustable)	
Equalization Charge	59.2 VDC (adjustable)	
Deep-Discharge Protection	44 VDC (adjustable)	
Reconnect Level	51.2 VDC (adjustable)	
Overvoltage Protection	66 VDC	
Indervoltage Protection	38.4 VDC	
Nax. PV Panel Voltage	450 VDC	
Max. Usable PV Power	4800 W	
Nax. PV Array Power	6000 W	
C Frequency	50/60 Hz auto recognition	
C Output Voltage	220-240 VAC ±5% (adjustable)	
Surge Power	2x rated power for 5 seconds	

Туре	PSW-H-5KW-230/48V	
Inverter Efficiency (from Battery)	>93 % peak	
Inverter Efficiency (from PV)	>96 % peak	
Idle Self-Consumption	< 40 W on, < 14 W Green Mode	
Grounding	Galvanically isolated battery allows positive or negative grounding	
Ambient Temperature	-10 to +50 °C	
Storage Temperature & Humidity	-15 to +60 °C, 5-95 % (non-condensing)	
Max. Altitude	4,000 m above sea level, 1 % power de-rating per 100m above 1,000 m above sea level	
Battery Type	Lead acid (gel, AGM, flooded), LiFePO4	
Datalogger	60 days	
Max. Wire Cross Section	Battery: 50 mm <sup>2</sup> (AWG 0), PV: 16 mm <sup>2</sup> (AWG 4), AC: 10 mm <sup>2</sup> (AWG 7)	
Dimensions (WxHxD)	143 x 309 x 468 mm / 5.6 x 12.2 x 18.4 in	
Weight	11.8 kg / 26 lbs	
Ingress Protection	IP21	
Certificates	CE compliant, RoHS compliant	
Warranty	2 years	



# What is Any-Grid™?

raditionally, the energy industry defines power systems relative to their access to the grid as Off-Grid or On-Grid. At 'hocos, we believe energy access should be available under 'Any-Grid<sup>™</sup> conditions whether you have full or partial ccess to renewable energy and/or grid power, and if energy sources are unreliable. The Phocos Any-Grid<sup>™</sup> Hybrid hverter Charger Series provides flexible energy access solutions that optimize the use of locally available energy resources hat can adapt as access to resources changes over time.

### Any-Grid<sup>™</sup> (Off-Grid and/or On-Grid) Capability

