

YMTGW

Pushbutton silver-coloured, non-transparent lens



General Data

Type reference	Y(M)T(L)(G)(x)(L_yyyy)(zzzzzz_zz)
Description	Short-stroke pushbutton mYnitron
Approvals	CE, cURus
Contact type	1NO
Degree of protection	IP65 / IP67
Operation travel	1,0 mm
Connection type	Faston terminals 2.8 mm x 0.5 mm
Contact material	snap disk: stainless steel 1.4310 gold-plat. counter contact: CuZn37, gold-plat
Max. storage temperature	-40°C ... 80°C
Max. operating temperature	-25°C ... 70°C
Mechanical life	500,000 switching cycles
Electrical life (rated load)	500,000 switching cycles at rated load
Contact resistance NO	< 100 mOhm
Min. current	10 uA
Min. voltage	20 mV
Bouncing time NO	< 5ms

Electrical data acc. to IEC/EN 60947-5-1 (VDE 0660 Sect. 200)

	alternate current	direct current
Utilisation category	AC12	DC12
Rated insulation voltage Ui	42 V	42 V
Rated operating voltage Ue	35 V	35 V
Rated operating current Ie	100 mA	100 mA
Breaking capacity	1 W (ohmic load)	1 W (ohmic load)
Continuous thermal current	100mA	100mA

Technical Data - Lamp

Lamp socket	none, with integrated LED
-------------	---------------------------



Max. lamp voltage	10...32V
Max. lamp output	20 mA (18...22 mA)
Definition	+ ...anode, - ...cathode

Additional Data

Mounting aperture	16.2 mm
Tightening torque (mounting nut)	max. 0.7 Nm
Mounting grid	25mm x 25mm
Mounting position	any
Standards	IEC/EN 60947-5-1
Overvoltage category	II
Pollution degree	2

Electrical Features

B10	600.000
-----	---------

Note

- contact type 1 NO
- perceptible, defined pressure point
- front ring metallic or black (standard)
- incl. lens
- various labelling options (standard symbols or customised)

Type variants:

Y(M)T(L)(G)(x)(L_yyyy)(zzzzzz_zz)

(M) ... front ring titanium lacquered

(L) ... with illuminating option, LED

(G) ... non-transparent lens

(x) ... available lens colours x = {R...red,

Y...yellow, B...blue, G...green, W...white,

S...black}

(L_yyyy) ... printed with standard symbol

(zzzzzz_zz) ...customised printing

- Use partially insulated Faston terminals!

Recommended Schlegel type: "FHTI2,8x0.5_01"

0.5-1.5mm² (AWG 20-16)

-30°C - 75°C

- NO: 3-4

- LED: +/-

- The Faston terminals are not suitable for hand soldering

- The max. tightening torque mounting nut to be observed (0.7 Nm) !



Data acc. to UL 60947-5-1

Ratings max. 30 Vac or 42.4 V peak, 100 mA, Class 2

Illumination 10-32V DC 20 mA


Remark

- Nur für Class 2 Spannungsversorgung oder begrenzte Spannungs- / Stromwerte
- For Class 2 Power Source or Limited Voltage / Limited Current only
- Pour classe 2 source d'alimentation ou tension limitée / courant limitée uniquement


Illustration:



Dimensional drawing:



Wiring diagram:



Drilling pattern:

