



Discover more details and matching accessories online!

The compact all-round model with robust stainless steel weighing plate for use in laboratories, industries, and for teaching

Features

- Thanks to its compact, robust design, its bright display and high precision, this range is ideal for use in laboratories, quality control, production as well in schools and universities for teaching
- Large, shock proof weighing plate made from stainless steel, can be removed and therefore is hygienic and easy to clean
- **1** Particularly flat design
- Ergonomically optimised key pad with large keys and a high-contrast LCD display
- **2** Secure and non-slip positioning with rubber feet
- Level indicator and levelling feet for precise levelling of the scale, fitted as standard, to give the most accurate weighing result
- Adjusting program CAL for quick setting of the balance accuracy, external test weights at an additional price, see *test weights*

Technical data

- Large backlit LCD display, digit height 22 mm
- Dimensions weighing surface, stainless steel
 - A** ø 105 mm
 - B** W×D 120×120 mm, see larger picture
- Overall dimensions W×D×H 225×160×50 mm
- Optional battery operation, 2×1.5 V AA not included in scope of delivery, operating time up to 70 h
- Mains adapter external, standard
- Net weight approx. 0,50 kg
- Permissible ambient temperature 5 °C/40 °C

STANDARD

OPTION

Model	Weighing capacity	Readability	Reproducibility	Linearity	Weighing plate	Options
						Calibr. Certificate
	[Max]	[d]				DAkkS accr. KERN
	g	g	g	g		
KERN						
EHA 500-2	500	0,01	0,03 g	± 0,03	A	963-127
EHA 500-1	500	0,1	0,3 g	± 0,3	A	963-127
EHA 1000-1	1000	0,1	0,3 g	± 0,3	B	963-127
EHA 3000-1	3000	0,1	0,3 g	± 0,3	B	963-127
EHA 3000-0	3000	1	3 g	± 2	B	963-127