

Lightning and surge protection
VPU ZPA I 3+1 300/7,5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Lightning arresters for 40 mm rail systems

- Simple and safe to use and install
- Complete and permanent status control
- Leakage current free surge protection
- Application-specific application classes with 7.5 kA and 12.5 kA discharge current

General ordering data

Type	VPU ZPA I 3+1 300/7,5
Order No.	2674460000
Version	Surge voltage arrester, Low voltage, Leakage-current-free, TN-C-S, TN-S, TT, $U_P(L/N-PE) \leq 1.5$ kV
GTIN (EAN)	4050118686838
Qty.	1 pc(s).

Lightning and surge protection VPU ZPA I 3+1 300/7,5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	47 mm	Width (inches)	1.85 inch
Height	229 mm	Height (inches)	9.016 inch
Depth	99 mm	Depth (inches)	3.898 inch
Net weight	100 g		

Temperatures

Humidity	5...95 %, no condensation	Operating temperature, max.	70 °C
Operating temperature, min.	-40 °C	Storage temperature, max.	70 °C
Storage temperature, min.	-40 °C	Operating temperature	-40 °C...70 °C
Storage temperature	-40 °C...70 °C		

Rated data UL

Altitude	≤ 4000 m
----------	----------

General data

Altitude	≤ 4000 m	Colour	grey
Design	miscellaneous	Optical function display	green = OK; red = arrester is defective - replace
Protection degree	IP30, in combination with the cover	Segment	Power distribution
Suitable for	Count-in installation (leakage current free)	UL 94 flammability rating	V-0
Version	Leakage-current-free		

Rated data IEC / EN

Rated voltage (AC)	240 V	Voltage type	AC
Max. continuous voltage, U_c (AC)	300 V	Max. continuous voltage, U_c (N-PE)	305 V
Low voltage network	TN-C-S, TN-S, TT	Discharge current I_n (8/20µs) N-PE	80 kA
Discharge current I_{max} (8/20µs) N-PE	100 kA	Discharge current I_n (8/20µs) wire-PE	20 kA
Discharge current I_{max} (8/20µs) wire-PE	50 kA	Lightning test current I_{imp} (10/350 µs) (L-PE)	7.5 kA
Lightning test current, I_{imp} (10/350 µs) (N-PE)	30 kA	Frequency range, max.	60 Hz
Frequency range, min.	50 Hz	Fuse	No Fuse necessary ≤160 A gG
Short-circuit current rating I_{SCCR}	25 kA	Follow-on current extinguishing capability I_{fi}	Not available due for technical reasons
Standards	IEC61643-11, EN61643-11	Energy coordination (≤10 m)	Type I, Type II, Type III
Protection level U_p (typ.)	≤ 1.5 kV	Protection level U_p at I_N (N-PE)	≤ 1.5 kV
Leakage current at U_n	5 µA	Temporary surge voltage (over-voltage) - TOV	442 V
Requirements category acc. to IEC 61643-11	Type I, Type II	Requirements class, acc. to EN 61643-11	T1, T2
Response time	≤ 100 ns	Signalling contact	No
Suitable for	Count-in installation (leakage current free)		

Lightning and surge protection

VPU ZPA I 3+1 300/7,5

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data

Connection data

Wire connection method	Screw connection	Type of connection	Clamped
Tightening torque, max.	4.5 Nm	Clamping range, min.	16 mm ²
Clamping range, max.	35 mm ²	Conductor cross-section, flexible, AEH (DIN 46228-1), min.	16 mm ²
Conductor cross-section, flexible, AEH (DIN 46228-1), max.	25 mm ²	Connection cross-section, stranded, min.	16 mm ²
Connection cross-section, stranded, max.	35 mm ²		

Classifications

ETIM 6.0	EC000941	ETIM 7.0	EC000941
eClass 9.0	27-13-08-05	eClass 9.1	27-13-08-05
eClass 10.0	27-13-08-05		

Product information

Product information	Only applicable to IT power systems where the earth on the distribution transformer is interconnected with the earth on the consumer side (RE=RA in Figure 44.A1 of IEC 60634-4-44:2018).
---------------------	---

Approvals

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of Conformity	CE VPU ZPA
User Documentation	Manual

Lightning and surge protection VPU ZPA I 3+1 300/7,5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

