



CS Y1 Miniature “S”-load/force measuring cell made of stainless steel

Technical data

- High precision
(comprehensive Error 0,05 % F.S.)
- Accuracy in accordance with OIML C1
- RoHS compliant
- Protection against dust and water splashes
IP65
- Stainless steel
- Area of application: Tensile and compressive
applications, mass and force measurement
- Suitable for force test stands, hanging scales,
silo scales and various other balances
- 4-wire connection
- Nominal sensitivity: 1,3 – 2 mV/V,
depending on nominal load
- Cable length: 2 m



Model Nominal load


SAUTER

CS 1-Y1	1 kg/10 N
CS 2-Y1	2 kg/20 N
CS 5-Y1	5 kg/50 N
CS 10-Y1	10 kg/100 N
CS 20-Y1	20 kg/200 N

CO Y1 · CO Y2 · CO Y3 · CO Y4 Miniature cylindrical load cell made of stainless steel

Technical data

- RoHS compliant
 - Suitable for weight measurement
as well as force and force test stands
 - 4-wire connection
- CO Y1 · CO Y4**
- High precision (comprehensive Error 0,5 % F.S.)
 - Accuracy in accordance with OIML G5
 - Area of application: Compressive applications
 - Nominal sensitivity: 1,0 – 1,5 mV/V, depending
on nominal load
- CO Y2 · CO Y3**
- High level of accuracy, Comprehensive error
CO Y2: 0,5 % F. S. | CO Y3: 0,1 % F. S.
 - Accuracy in accordance with
OIML G5 (CO Y2) | G10 (CO Y3)
 - Area of application: Tensile and compressive
applications
 - Nominal sensitivity: 1,5 – 2 mV/V, depending
on nominal load
 - Cable length: 2 m



Model Nominal load

SAUTER

CO 10-Y1	10 kg/100 N
CO 20-Y1	20 kg/200 N
CO 50-Y1	50 kg/500 N
CO 100-Y1	100 kg/1 kN
CO 200-Y1	200 kg/2 kN
CO 500-Y1	500 kg/5 kN
CO 1000-Y1	1000 kg/10 kN
CO 2000-Y1	2000 kg/20 kN

CO 10-Y2	10 kg/100 N
CO 20-Y2	20 kg/200 N
CO 50-Y2	50 kg/500 N
CO 100-Y2	100 kg/1 kN
CO 200-Y2	200 kg/2 kN
CO 500-Y2	500 kg/5 kN
CO 1000-Y2	1000 kg/10 kN
CO 2000-Y2	2000 kg/20 kN

CO 5-Y3*	5 kg/50 N
CO 10-Y3*	10 kg/100 N


CO 5-Y4*	5 kg/50 N
CO 10-Y4*	10 kg/100 N

! * ONLY WHILE STOCKS LAST

CO Y5 Tension and compression force measuring cell made of stainless steel

Technical data

- Accuracy in accordance with OIML R60 G1
- CE and RoHS compliant
- Protection against dust and water splashes
IP66 (in accordance with EN 60529)
- Stainless steel
- Very low design
- Suitable for test stands, force gauges,
automation systems, etc.
- 4-wire connection
- Nominal sensitivity:
CO 0.5-Y5, CO 1-Y5: 1 mV/V
CO 5-Y5, CO 10-Y5: 2 mV/V
- Cable length: 2 m



Model Nominal load

SAUTER

CO 0.5-Y5	500 g/5 N
CO 1-Y5	1 kg/10 N
CO 5-Y5	5 kg/50 N
CO 10-Y5	10 kg/100 N

**Discover more details and matching
accessories online!**