



No.	Changes and/or Note No.	Date	Intr.	No.	Changes and/or Note No.	Date	Intr.



PARTS OPTION



SCREWS
($\phi 4.2 \times 14.58 \text{mm}$)

SPECIFICATION

MATERIAL

WIRE :PVC WIRE COMPOUND UL1007
CASE : ABS PA-707 NATURE CHROMIUM COATING
Insulator: P.B.T & Glass fill reinforced UL94V-0
Contacts: Brass(standard);Phosphor Bronze(choose)
Shell: ABS UL94HB Finished Metalized

Rivet,Boardlock: Brass

CONTACT PLATING

Underplate: 50m" Nickel
Contact area: 1m" Selective Gold

ELECTRICAL CHARACTERISTICS

Operation voltage: 250 VAC max.
Current rating: 3 Amps max.
Contact resistance: 15 mohms max.
Insulation resistance: 3000 Mohms min @ 500 VDC
Dielectric withstanding voltage: 1000 VAC / minute
Operating temperature: -55, C TO +105, C

WIRE SPECIFICATION COUNT		
BLACK	M-M	2
BROWN	M-M	2
RED	M-M	2
ORANGE	M-M	2
YELLOW	M-M	2
GREEN	M-M	1
BLUE	M-M	1
VIOLET	M-M	1
GRAY	M-M	1
WHITE	M-M	1

DATE	DRAWN	SCALE	MATERIAL TYPE	
	APPROVED		REPLACES	
			15-way Male to 15-way Male-Metalized GA-1515-MM-M-K	
			DRAWING No	2111-0105-02