



Connection Method



NOTES:

ELECTRICAL:

- 1. Contact Resistance : 20MΩ MAX
- 2. Insulation Resistance : 500MΩ MIN @ 500V DC
- 3. Withstand Voltage : DC 1000V AC 700V RMS 60Hz, 1MIN
- 4. Component testing for Cat.6A to ISO/IEC 11801 Ed. 2. 2:2011-06
DIN EN 50173-1:2011-09
TIA/EIA-568-C. 2 (2009-08)

ENVIRONMENTAL:

- 1. Storage temperature : -40℃~+70℃
- 2. Operation temperature : -10℃~+60℃
- Operation humidity : 30%~80%
- Storage humidity : 30%~80%

MECHANICAL

- 1. RJ45 Contact Life: 750 Times Min
 - 2. Plug inforce: <30N
- RoHS 2.0 and REACH Compliant
F/N:29212c281

MATERIAL LIST:

④	Shrapnel	PC White	1	
③	Contact	8P8C Gold Plated	16	
②	Housing	Zinc Alloy	1	
①	PCB	FR-4, t=0.8	1	

NO	MAT. NAME	DESCRIPTION	QT' Y	REMARK
BY	CHK	REVISION RECORD MODIFICATIONS	DATE	REV.

CUSTOMER		CN	ITEM NO.	2265799		
PRODUCT NAME	CAT. 6A STP RJ45 F/F Coupler Keystone jack Type Zinc Alloy Housing		UNO ITEM NO.	277322	UNIT	MM
		NEW	2020/03/04	A0	DRAWNBY	CHECKBY
					ALVAN	ALVAN
						2020/03/04