SPECIFICATIONS

[General Specifications]

		[6	General Specifications		
	Model	NBM-D88NN			
Rate	d Voltage		24VDC		
Operating Voltage Range		Rated Voltage ±10%			
Rated Curr Consumpt	May	0.6A			
Operating Ambient Temperature		0°C to +40 °C			
Operating Ambient Humidity		20-80% (No condensation)			
Storage Ambient Temperature		-20°C to +65°C			
Storage Ambient Humidity		Less than 80% (No condensation)			
Mounting Location		Indoors			
Mounting Direction		Upright			
	tion Rating	IP 20 (IEC 60529)			
Vibration Resistance		9.8m/s² (IEC 60068-2-6)			
Mass (Tol	erance ±10%)	1.15 kg			
	Dimensions	Refer to the Outer Dimension Drawing			
Conform	ity Standards	RoHS Directive (EN 50581)			
	•		FCC Part 15 Subpart B Class A		
		CAN/CSA C22.2 UL/CSA 60950-1			
		EMC directive (EN 55032 (ClassA), EN 55024)			
			KC(KN61000-6-4,KN61000-6-2)		
Communi	cation Method		Ethernet (Conforms to the IEEE 802.3)		
	Physical Layer	10BASE-T/100BASE-TX (Auto-negotiation • Full Duplex/Half Duplex)			
	Data Link Layer		CSMA/CD		
	Network Layer	IP•ARP•ICMP			
	Transport Layer	TCP•UDP			
Application Layer		HTTP • SNMP(V1,V2c) • RSH • SMTP • NTP			
			POP3 - DNS - Socket(PHN - PNS) - DHCP		
Interface	USB Port	USB2.0/1.1 TYPE-A 1ch			
	Serial Port	RS	232C D_SUB_9P(Used for expanding additional functions)		
Power Output		One screw Terminal Block 24VDC±10%, maximum 200mA			
Digit	al Output	Non-voltage contact output; "A" contact (setup can be changed for "B" contact)			
Nu	imber of Contacts		8		
		Dowlo 1 to 7	(30V DC @ 3A) inrush current under 5A		
_	Contact Consoity	Ports 1 to 7	Minimum (1mA, 5VDC,Reference)		
	Contact Capacity	Port 8	(30V DC @ 3A) inrush current under 78A (TV-5 rating) Minimum (5V DC, 10mA) *		
	Wire Diameter	Solid Wire:	00.4-1.2mm (AWG26-16) /Stranded Wire:0.2-1.25mm ² (AWG24-16)		
	Wiring Method	Screwless Terminal Block			
Digital Input		Non-voltage Contact			
Nu	imber of Contacts	8			
Transistor Input		NPN Transistor			
Contact Capacity		Output "ON" current @ 6mA or less per channel. Terminal OFF condition Voltage: 24V			
	Wire Diameter		Solid Wire:φ0.4-1.2mm (AWG26-16)/Stranded Wire:0.2-1.25mm ² (AWG24-16)		
	Wire Diameter	SOUG WITE O			

PATLITE Corporation

Input Reaction Time	110msec or more	
Output Response Time	200msec or less	
Display Part	18 green LED (power, status, DO x8 Contacts, DI x8 Contacts)	
Operation Part	"Select" Switch, "Reset" Switch, "Clear" Button, "Mode" Switch	
Accessory	Rubber Feet	
Optional Parts	Server Rack Mounting Bracket (NBM-ANG)	
Remarks	Conforms to the CE requirements	
	When connecting a product with a large inrush current, such as a revolving light etc., wire it	
	to output terminal Port 8.	

[Fanctional Specifications]

The contact output of this product is controlled by contact input information, or by software commands. Moreover, when abnormalities occur, the NBM can control contact output and command transmissions with it's network monitoring function.

Digital Output	External instruments are connected and the contacts are controlled for ON/OFF outputs.		
Bigital Gatpat	The status condition of a non-voltage contact input can be detected.		
	When detection occurs, the following operations will be executed:		
Digital Input	Digital Output ON/OFF, RSH Command Transmission, PNS/PHN Socket Transmission, E-		
	mail Transmission, SNMP TRAP Transmission		
	When pressing the "Clear" button, the following actions are executed:		
"CLEAR" Button	Digital output ON/OFF (a default is turned off), E-mail transmission, RSH command		
OLL/IIV Button	transmission, PNS/PHN socket transmission, SNMP TRAP transmission		
"Reset" Switch	The product is rebooted.		
TRAP Transmission	An SNMP TRAP (V2C) is sent when an event occurs.		
Trutt Transmission	All Crivin 110 to (V20) to cont when all event econic.		
	When an SNMP TRAP is received, the following operations are executed:		
TRAP Reception	Digital Output ON/OFF, RSH Command Transmission, PNS/PHN Socket Transmission, E-		
	mail Transmission,SNMP TRAP Transmission		
E-mail Transmission	Sends an E-mail when an event occurs. (up to 8 addresses).		
RSH Command Transmission	Sends an RSH command when an event occurs.		
	When an RSH command is received from an external device, it controls the ON/OFF of the		
RSH Command Reception	digital output and acquires the contact status.		
0 1 1 5 11	When receiving a PNS or PHN command, it controls the ON/OFF of the digital		
Socket Reception	output and acquires the contact status.		
Socket Transmission	When an event occurs, it sends a PNS or PHN command.		
Test Function	The RSH command for checking operation. The Digital Output operates in sequential order.		
Ping Monitoring	The PING Command is sent to an external device to check it's connection status.(Max. 24)		
Application Monitor	The operation status of a working application to an external device can be checked.		
Data Log	A status log and operation log are saved.(Transmission to syslog server / Save to USB memory)		
ONINE OFFICET	The digital output can be controled, contact information can be acquired, traps can be sent		
SNMP SET/GET	and received (MIB file application) (V1, V2C)		
Ti 0 "	Automatically correct time (register and connect to an NTP server)		
Time Correction	The time correction is reflected on the PC.		
"Select" Switch	The operation for each mode can be determined.		
Web Setup Tool	The tool necessary for making various settings on the WEB screen.		
PNS/PHN	Remote control of NHL Series and PHN series with Socket Communication and PNS/PHN		
Series Control Function	control signal.		
No.NBM-D88NN-W18A-2_4			

Xml Function	Obtain the data for the Input/Output contact status in xml format.	
PNS Manager Function	It corresponds to the PNS manager (Network Setup Application).	
Initialization Function	=Web Setup Tool= Factory default. Initialization other than Network Setup. = "Mode" Switch = Network Setup initialization. Factory default. Password initialization.	
Mode Change	Change to the following mode with the "Mode" Switch. 0. Normal Mode 1. Configuration Download Mode 2. Configuration Upload Mode 3. Network Setting Initialization Mode 4. Factory Default Mode 5. Reserved 6. Firmware Update Mode 7. Password Initialization Mode 8. Reserved 9. Reserved * Initialization : Return to factory default setup.	
Configuration Data Setup	Save / write setting information with Web setup tool and USB memory.	
"A" Contact/"B" Contact Changeover	The Web Setup Tool can be used to logically set between the "A" contact or "B" contact.	
Contact Status Display	The contact status is displayed on the WEB screen.	
USB	Log data can be stored onto USB memory (storage place can be changed to internal memory or USB memory). Update firmware onto USB memory Upload/download Configuration data	
Firmware Update	Update using the Web Setup Tool Update using a USB memory	
Digital Input Condition Setup	Setup the digital input detection method to the following method. AND detection: It detects when specified multiple digital inputs turn ON. Number of Detection Times: Detects when the digital input is turned ON for the specified number of times. Continued Detection Duration: Detects when the digital input continues to be ON for the specified time.	

[Recommended AC Adaptor Specifications]

[Recommended AC Adaptor Specifications]							
DC Output	Voltage	24V DC ±5%					
	Current	0.75A to 1A max.					
	Plug Length	9.5mm or more					
	Plastic Housing	10mm dia. or less					
	Plug Connector Outer Diameter	5.5mm dia.					
	Plug Connector Inner Diameter	2.1mm dia.					
	9.5						
No.NBM-D88NN-W18A-3_4							

