



PIN OUT

A1	—	A1	B1	—	B1
A2	—	A2	B2	—	B2
A3	—	A3	B3	—	B3
A4	—	A4	B4	—	B4
A5	—	A5	B5	—	B5
A6	—	A6	B6	—	B6
A7	—	A7	B7	—	B7
A8	—	A8	B8	—	B8
A9	—	A9	B9	—	B9
A10	—	A10	B10	—	B10
A11	—	A11	B11	—	B11
A12	—	A12	B12	—	B12

NOTES:

1. Electrical test:

- (1). 100% open short & miss wire test;
- (2). Insulation resistance: DC 300V 10M Ω Min;
- (3). Contactor resistance: 3 Ω Max;

Up and down angle 90 degrees

Data Transfer: 10Gbps Voltages: 5V Current: 3A,
RoHS 2.0 and REACH Compliant

2. ENVIRONMENTAL:

Operation temperature : -10 $^{\circ}$ C ~ +60 $^{\circ}$ CStorage temperature : -20 $^{\circ}$ C ~ +75 $^{\circ}$ C

Operation humidity : 10% ~ 85%

Storage humidity : 10% ~ 85%

MATERIAL LIST:

③	Moulding	PVC Moulding Black	1	
②	Connector	USB 3.1 C Female, Black insulation The Pin Gold Plating, the Shell For Nickel plating	1	
①	Connector	USB 3.1 C male, Black insulation The Pin Gold Plating, the Shell For Nickel plating	1	

NO.	PARTS NAME	SPECIFICATION STANDARD	QT' Y	REMARK
		NEW		2018-08-28
BY	CHK	REVISION RECORD MODIFICATIONS		DATE
				REV.

[REDACTED]					
CUSTOMER	CN	ITEM NO.	2269116		
PRODUCT NAME	USB 3.1 GEN2 Type C male to C Female 90 degree angle Adapter	ITEM NO.	750098	UNIT	MM
DRAWNBY	CHECKBY	APPOBY	DATE		
wbs	Alvan		2018-08-28		