

## Features

- Compliant to DoE 2016 (Level VI)
- ErP Stage 2, NRCan & GEMS Level VI
- No Load Power Consumption < 0.1 W
- Regulated Output with Low Ripple Noise
- 1 Year Warranty



## Marks / Approvals



## Specifications

Product similar to photo, variations possible.

	MODEL	Voltage	Min. Load	Max. Load	Max. Power
	ATS 024T-W050	5.0 V	0.0 A	4.0 A	20.00 W
	ATS 024T-W060	5.9 V	0.0 A	3.5 A	20.65 W
	ATS 024T-W061	5.9 V	0.0 A	4.0 A	23.60 W
	ATS 024T-W070	7.0 V	0.0 A	3.0 A	21.00 W
	ATS 024T-W075	7.5 V	0.0 A	3.0 A	22.50 W
	ATS 024T-W090	9.0 V	0.0 A	2.5 A	22.50 W
	ATS 024T-W120	12.0 V	0.0 A	2.0 A	24.00 W
	ATS 024T-W150	15.0 V	0.0 A	1.6 A	24.00 W
	ATS 024T-W240	24.0 V	0.0 A	1.0 A	24.00 W
	ATS 024T-W480	48.0 V	0.0 A	0.5 A	24.00 W
INPUT	<b>Voltage</b>	AC 100 V – 240 V			
	<b>Frequency</b>	50 Hz - 60 Hz			
	<b>Current</b>	0.58 A max.			
	<b>Protection</b>	Internal Primary Current Fuse, Inrush Limiting			
OUTPUT	<b>Load Regulation</b>	± 5 % (typical)			
	<b>Ripple</b>	1 % – 2 % V p-p max. for output voltage at full load			
	<b>Transient Response</b>	0.5 ms for 50 % load change typical			
	<b>Leakage Current</b>	0.25 mA max.			
	<b>Protection</b>	Short circuit Protection • Over Voltage Protection • Over Current Protection			
OTHERS	<b>Cooling</b>	Convection			
	<b>Efficiency</b>	DoE Level VI • Energy Star • ErP Stage 2 • NRCan & GEMS Level VI Certified			
	<b>Holdup Time</b>	10 ms at full load			
	<b>Dielectric Withstand</b>	AC 3000 V Primary – Secondary			
	<b>MTBF</b>	300,000 calculated hours at 25 °C by telcordia SR-332			
ENVIRONMENT	<b>Temperature</b>	Operating: 0 °C – 40 °C / Storage: -20 °C – 80 °C			
	<b>Humidity</b>	Operating: 20 % RH – 80 % RH / Storage: 10 % RH – 90 % RH			
<b>EMI Conduction &amp; Radiation</b>	Compliance to EN 55022 Class B				
<b>Harmonic Current</b>	Compliance to EN 61000-3-2, -3				
<b>EMS Immunity</b>	Compliance to IEC 61000-1-2, -3, -4, -5, -6, -8, -11				
<b>Safety</b>	IEC / EN / UL 62368-1 • IEC 60950-1 • CE • RCM • PSE • BSMI (approvals may vary with input plug type)				
<b>Case Dimensions</b>	72 mm × 34 mm × 90 mm (Europlug version)				
<b>Weight</b>	154 g (Europlug version)				