


PARTS OPTION



SCREWS
($\phi 4.2 \times 15.0 \text{ mm}$)

No.	Changes and/or Note No.	Date	Intr.	No.	Changes and/or Note No.	Date	Intr.

SPECIFICATION

MATERIAL

WIRE :PVC WIRE COMPOUND UL1007

Insulator: P.B.T & Glass fill reinforced UL94V-0

Contacts: Brass

Shell: **ABS UL94HB Finished Metalized**

Rivet,Boardlock: Brass

CONTACT PLATING

Underplate: 50m" Nickel

Contact area: 1m" Selective Gold

ELECTRICAL CHARACTERISTICS

Operation voltage: 250 VAC max.

Current rating: 3 Amps max.

Contact resistance: 15 mohms max.

Insulation resistance: 3000 Mohms min @ 500 VDC

Dielectric withstanding voltage: 1000 VAC / minute

Operating temperature: -55°C TO $+105^{\circ}\text{C}$

WIRE SPECIFICATION COUNT

BLACK	M-M	1
BROWN	M-M	1
RED	M-M	1
ORANGE	M-M	1
YELLOW	M-M	1
GREEN	M-M	1
BLUE	M-M	1
VIOLET	M-M	1
GRAY	M-M	1

DATE	DRAWN	SCALE	MATERIAL TYPE	
	APPROVED		REPLACES	
		9-way Male to 9-way Male-Metalized GA-0909-MM-M-K		
				DRAWING No 2111-0105-01