


No.	Changes and/or Note No.	Date	Intr.	No.	Changes and/or Note No.	Date	Intr.



SPECIFICATION

MATERIAL

WIRE :PVC WIRE COMPOUND UL1007

Insulator: P.B.T & Glass fill reinforced UL94V-0

Contacts: Brass(standard);Phosphor Bronze(choose)

Shell: ABS UL94HB Finished Metalized

Rivet,Boardlock: Brass

CONTACT PLATING

Underplate: 50m" Nicke

Contact area: 1m" Selective Gold

ELECTRICAL CHARACTERISTICS

Operation voltage: 250 VAC max.

Current rating: 3 Amps max.

Contact resistance: 15 mohms max.


Insulation resistance: 3000 Mohms min @ 500 VDC

Dielectric withstanding voltage: 1000 VAC / minute

Operating temperature: -55°C TO +105°C

WIRE SPECIFICATION COUNT		
BLACK	F-F	2
BROWN	F-F	2
RED	F-F	2
ORANGE	F-F	2
YELLOW	F-F	2
GREEN	F-F	1
BLUE	F-F	1
VIOLET	F-F	1
GRAY	F-F	1
WHITE	F-F	1

PARTS OPTION



DATE	DRAWN	SCALE	MATERIAL TYPE
	APPROVED		REPLACES
15-way female to 15-way female-Met. GA-1515-FF-M-K			DRAWING No 2111-0105-22