


UNO ITEM NO.	FN NO.	LENGTH
716066, 15	FN 29212c277c	15000+200/-0
716066, 20	FN 29212c277d	20000+200/-0



MATERIAL LIST:

⑦	Shell	ABS Black	4	
⑥	OUTER MOLD	PVC BLACK	3	
⑤	INNER MOLD	LD-PE	1	
④	PCBA	PCB-FE1.1S	2	
③	USB 2.0 A Female	USB A/F Solder Type, White PBT Insulation, The Pin Gold Plating, the shell for Nickel Plating +PCB and IC	1	
②	USB 2.0 A male	USB A/M Solder Type, White PBT Insulation, The Pin Gold Plating, the shell for Nickel Plating	1	
①	CABLE	UL2725 28#(TC)*1PR+24#(TC)*2C+AL -FOIL+D(28AWG BC)+B (64#)PVC: black OD:4.8±0.2MM	1	

NOTE:

1. Electrical test:
 - (1). 100% Practical application test;
2. Storage temperature : -20°C~+60°C
3. Operation temperature: 0°C~+50°C
4. Operation humidity: 10%~85%
5. Storage humidity: 10%~85%
6. RoHS 2.0 and REACH Compliant
7. PRINTING: E***** 兄 AWM 2725 80° C 30V VW-1 28AWG/1P AND 24AWG/2C USB2.0 CABLE

NO.	PARTS NAME	SPECIFICATION STANDARD	QT'Y	REMARK
		NEW	2020-04-08	A
BY	CHK	REVISION RECORD MODIFICATIONS	DATE	REV.

CUSTOMER	ITEM NO.	UNO ITEM NO.	UNIT	MM
		716066		
PRODUCT NAME	USB 2.0 A male TO A Female Cable with 2 IC			
DRAWNBY	CHECKBY	APPOBY	DATE	
Alvan	Alvan		2020-04-08	