DIGITUS®



Industrial 4-port Gigabit PoE+ Switch with 2 x SFP uplink - DN-651109



Industrial 8-port Gigabit PoE+ Switch with 2 x SFP uplink - DN-651110

User Manual

DN-651109 / DN-651110

Package Contents

Check the following contents of your package:

- PoE Switch x 1
- User Guide x1
- Accessories

If any part is lost and damaged, please contact your local agent immediately.


Introduction

The DIGITUS® Industrial Gigiabit PoE Switch is designed for harsh environments where it is exposed to moisture, temperature fluctuations and vibration. With a temperature range of -40°C to 75°C, the Industrial Gigabit PoE Switch can be used under the most adverse conditions. The PoE ports with IEEE802.3af/at support can supply PoE capable devices with up to 30 W per port. It ensures a constant availability in highly sensitive areas such as transport, production, traffic and safety monitoring. The simple plug and play system allows the Industrial Gigabit Switch to be quickly integrated into the respective environment. With its Gigabit connectivity and SFP Uplink Ports, the Industrial Gigabit Switch is a flexible, cost-effective solution for the industrial environment.

Hardware Description

Front Panel

The Front Panel Consists of Ethernet Ports. The LED indicators are also located on the panel.



DN-651109 DN-651110

DIP Switch

The DIP switch located on the panel.

Flow Control ON: prevents data loose from mass data transmission and slow down the network speed. It is suitable for network environment where the network is shared to public.


FLOW Control OFF: the factory default mode. It performs normal data transmission. It is suitable for home and office network environment.

LED indicator

LED	Color	Function	
PWR	Green	Off: No Power supply	
		Light: Indicates the switch has power	
LNK/ACT	Green	Off: No device is connected to the	
		corresponding port	
		Light: Indicates the link through that port is	
		successfully established at 1000Mbps	
		Blink: Indicates that the Switch is actively	
		sending or receiving data over that port	
	Orange	Off: No device is connected to the	
		corresponding port	
		Light: Indicates the link through that port is	
		successfully established at 10/100Mbps	
		Blink: Indicates that the Switch is actively	
		sending or receiving data over that port	
PoE	Orange	Off: No PoE powered device (PD)	
		connected	
		Light: There is a PoE PD connected to be port	
		Blink: Indicates port abnormal PoE function	

Upper Panel

The upper panel has a standard 5-Pin industrial power input terminal for double redundant power backup and accepts DC power input.



Power input


This unit provides a 5-pin terminal block. It can be operated using 48-57 V DC power source. Always make sure your input voltage is within this supported voltage range.

To connect power:

This unit supports two power inputs. Follow the printed polarity for +V1-, +V2- and ground. Connect positive wires to V+, connect negative wires to V-, and connect a neutral wire to the ground mark.

- +V1- is for power input one connection (PWR1).
- +V2- is for power input two connection (PWR2).

Figure:



WARNING:

Always SHUT OFF power source to connect power wire.

WARNING:

Any exceeded input voltage will not make this unit function and may damage this unit.

Grounding column

The switch already comes with lightning protection mechanism. You can also ground the switch through the PE (Protecting Earth) with Ground Cable.

Installation of the Switch

This part describes how to install your Ethernet Switch and make connections to it. Please follow the following instructions to avoid incorrect installation causing device damage and security threat.

- Before cleaning the switch, unplug the power plug of the switch first. Do not clean the switch with wet cloth or liquid;
- Do not place the switch near water or any damp area. Prevent water or moisture from entering the switch chassis;
- Do not place the switch on an unstable case or desk. The switch might be damaged severely in case of a fall;
- Ensure proper ventilation of the equipment room and keep the ventilation vents of the switch free of obstruction;
- Make sure that the operating voltage is the same one labeled on the switch;
- Do not open the chassis while the switch is operating or when electrical hazards are present to avoid electrical shocks.

DIN-Rail Mounting

The DIN-Rail is already screwed on the Industrial Equipment. Please refer to following figures and know how to hang the Industrial Equipment:

Step 1: Lightly press the button of DIN-Rail into the track.



Install Industrial Equipment in DIN-Rail mount.


Step 2: Check the DIN-Rail is tightly on the track.



Remove DIN-Rail Mounting

Step 1:

Please refer to following procedures to remove the Industrial Equipment from the track



Remove Industrial Equipment in DIN-Rail mount.

Step 2:

Lightly press the button of DIN-Rail for remove it from the track.

Specifications

	Industrial 4-Port Gigabit	Industrial 8-port Gigabit	
Model	PoE+ Switch with 2 x SFP	PoE+ Switch with 2 x SFP	
	Uplink	uplink	
Standard	IEEE802.3, IEEE802.3u, IEEE802.3az, IEEE802.3x,		
Standard	IEEE802.3af, IEEE802.3at, IEEE 802.3ab, IEEE 802.3z		
Network Media(Cable)	10BASE-T: UTP category 3,4,5 cable (≤100m) 100BASE-TX: UTP category 5 cable (≤100m) 1000BASE-T: UTP category 5e, 5 cable (≤100m) 1000BASE-TX: Gigabit SFP optical RJ45 electrical module 1000BASE-SX: Gigabit SFP multimode (850nm, LC, DDM) 1000BASE-LX: Gigabit SFP mode (1310nm, LC, DDM) 1000BASE-ZX: Gigabit SFP single mode (1550nm, LC, DDM)		
MAC Address Table	4K, Auto-learning, Auto-aging		
Transfer mode	Store-and-Forward		
Jumbo frame	9216 Byte		
Packet buffer	1.5M bit		
Switching Capacity	12Gbps	20Gbps	
Packet Forward Speed	8.9Mpps	14.88Mpps	
Input power supply	DC:48-57V		
Dimensions (L*W*H)	165*147*54mm		
Fan	Fanless		
PoE Port	Port1~4	Port1~8	
PoE Power on RJ45	Mode A 1/2(+),3/6(-)		
PoE Output	30W(Max)		
EEE	IEEE 802.3az		
Townsucture	Operating Temperature: -40°C ~ 75 °C (-40 °F ~167°F)		
Temperature	Storage Temperature: -40 °C ~ 80°C (-40 °F ~176°F)		
I I	Operating Humidity: 10% ~ 90% non-condensing		
Humidity	Storage Humidity: 5% ~ 90% non-condensing		
Surge Protection	Differential mode ±4KV Common mode ±6KV		
MTBF	>100000 hours		
Electrostatic standard	Contact 8KV,air 10KV		
·			

This is a Class A product. In home environment, this product may cause radio interference. In this case, the user may be required to take appropriate measures.

Hereby Assmann Electronic GmbH, declares that the Declaration of Conformity is part of the shipping content. If the Declaration of Conformity is missing, you can request it by post under the below mentioned manufacturer address.

www.assmann.com

Assmann Electronic GmbH Auf dem Schüffel 3 58513 Lüdenscheid Germany

