

DC/DC Converter

TEA 1HI Series, 1 Watt

- Highly cost efficient design
- I/O isolation: 4'000 VDC
- Operating temperature range
 -40 to +85 °C without derating
- 5 VDC (±10%) input voltage range
- Unregulated outputs
- Efficiency up to 78%
- Industry standard SIP-7 package
- 3-year product warranty



The TEA 1HI is an unregulated 1 Watt DC/DC SIP-7 converter series with high isolation which is specifically designed to offer a low-cost solution while keeping a high quality standard. This new series focuses on a simple but effective design approach, which minimizes component and labor cost and is complemented with a complete automatization of the manufacturing process. An operating temperature range from -40°C to 85°C without derating and an I/O-isolation of 4'000 VDC enables this series to cover many different applications. The industry standard package of this converter offers a broad application range in any space, cost critical application and is especially suited for high volume projects where simple but reliable products are needed.

Models						
Order Code	Input Voltage	Output Voltage	Output Current	Efficiency		
	Range	nom.	max.	typ.		
TEA 1-0505HI	4.5 - 5.5 VDC (5 VDC nom.)	5 VDC	200 mA	78 %		



Input Specification	ns	
Input Current	- At no load	28 mA typ.
Surge Voltage		9 VDC max. (1 s max.)
Recommended Input Fuse	,	500 mA (slow blow)
		(The need of an external fuse has to be assessed
		in the final application.)
Input Filter		Internal Capacitor

Voltage Set Accuracy		±3% max. (at 60 % load)
Regulation	- Input Variation (1% Vin step)	1.5% max.
	- Load Variation (10 - 90%)	9% max.
Ripple and Noise	- 20 MHz Bandwidth	50 mVp-p typ.
		100 mVp-p max.
Capacitive Load		1'000 μF max.
Minimum Load		Not required
Temperature Coefficier	nt	±0.03 %/K max.
Start-up Time		30 ms max.
Short Circuit Protection	1	Limited 1 s max., Automatic recovery

Safety Specifications Safety Standards - IT / Multimedia Equipment Designed for EN 62368-1 (no certification)

General Specificat	tions		
Relative Humidity			95% max. (non condensing)
Temperature Ranges	- Operating Temperature		-40°C to +95°C
	- Case Temperature		+105°C max.
	- Storage Temperature		-55°C to +125°C
Power Derating	- High Temperature		5 %/K above 85°C
		See application note:	www.tracopower.com/overview/tea1hi
Cooling System			Natural convection (20 LFM)
Switching Frequency			100 kHz typ. (Royer)
Insulation System			Functional Insulation
Isolation Test Voltage	- Input to Output, 60 s		4'000 VDC
Isolation Resistance	- Input to Output, 500 VDC		1'000 MΩ min.
Isolation Capacitance	- Input to Output, 100 kHz, 1 V		30 pF typ.
Reliability	- Calculated MTBF		2'000'000 h (MIL-HDBK-217F, ground benign)
Washing Process			Not allowed
Housing Material			Plastic (UL 94 V-0 rated)
Potting Material			Epoxy (UL 94 V-0 rated)
Pin Material			Phosphor Bronze (C5191)
Pin Foundation Plating			Nickel (1 µm min.)
Pin Surface Plating			Tin (3 µm min.), bright
Housing Type			Plastic Case
Mounting Type			PCB Mount
Connection Type			THD (Through-Hole Device)
Footprint Type			SIP7
Soldering Profile			Lead-Free Wave Soldering
			265 °C / 5 s max.
Weight			2 g

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.



II TRACO POWER

Environmental Compliance - REACH Declaration

- RoHS Declaration

- SCIP Reference Number

www.tracopower.com/info/reach-declaration.pdf

REACH SVHC list compliant **REACH Annex XVII compliant**

www.tracopower.com/info/rohs-declaration.pdf

Exemptions: 7a, 7c-I

(RoHS exemptions refer to the component concentration only, not to the overall concentration in the product (O5A rule).)


c75f4061-29c7-4520-81da-a857cb7778d0

Supporting Documents

Overview Link (for additional Documents)

www.tracopower.com/overview/tea1hi

Outline Dimensions



Dimensions in mm (inch) Tolerances: $x.x \pm 0.5$ ($x.xx \pm 0.02$) $x.xx \pm 0.25 (x.xxx \pm 0.01)$ Pin dimension tolerance: ±0.1 (±0.004)

Pinout		
Pin	Function	
1	+Vin (Vcc)	
2	–Vin (GND)	
5	–Vout	
7	+Vout	

 (0.020×0.010)