



42U shown

Premium 19" Server Cabinet

36U, Assembled, Black

Part No.: **715683**

EAN-13: 0766623715683 | UPC: 766623715683

The Intellinet Network Solutions Premium 19" Server Cabinet is designed with the data center in mind. This premium cabinet incorporates perforated front and rear doors to help ensure adequate airflow to your valuable network equipment. Its solid-steel panels are coated with electrostatic powder paint and the anodized aluminum frame helps secure and protect network equipment. Its zinc-plated, depth-adjustable mounting rails help ensure years of reliable use and sturdiness. The Intellinet Network Solutions Premium 19" Server Cabinet also features UL and RoHS certifications, reinforcing the quality of materials and construction to support networks that last.

Features:

- Ideal for all 19" rackmount applications
- Anodized aluminium frame
- Maximum static load of 2000 kg (4409 lb.)
- Perforated front and rear doors to support a free-air ratio of 67%
- Zinc-plated 19" mounting rails
- Antistatic powder coating on all panels
- Reversible front door
- Easily removable locking split side panels
- Multipoint door lock on front and rear doors

For more information on Intellinet products, consult your local dealer or visit www.intellinet-network.com.

All names of products or services mentioned herein are trademarks or registered trademarks of their respective owners. Distribution and reproduction of this document, and use and disclosure of the contents herein, are prohibited unless specifically authorized.

- Cable-entry and ventilation slots
- Ships fully assembled
- Three-year warranty

Specifications:

General

- 19"
- Height: 36U
- Color: Black RAL9005
- Certifications: RoHS, UL

Dimensions

- 1000 (L) x 800 (W) x 1767 (H) [mm] / 39.37 (L) x 31.5 (W) x 69.57 (H) [in.]

Package Contents

- Premium 19" Server Cabinet
- Four depth-adjustable mounting rails
- Four adjustable supporting feet
- Installation hardware



42U shown



42U shown
color: Gray shown



42U shown
color: Gray shown



42U shown
color: Gray shown



42U shown
color: Gray shown