



Power Delivery Wall Charger - 18 W

USB-C Power Delivery Port up to 18 W, Europlug, White

Part No.: [102094](#)

EAN-13: 0766623102094 | UPC: 766623102094

Device power in a portable, powerful Power-Delivery-capable charger

Enjoy complete charging power with the Europlug version of the Manhattan Power Delivery Wall Charger - 18 W. This wall charger's USB-C port uses Power Delivery (PD) technology to determine the power needs of your smartphone, tablet or other compatible device and supplies it at the fastest, safest rate it can. With its stylish, compact and ultra-modern design, the charger is the perfect power companion, intelligently safeguarding itself and your devices with its short-circuit-, overvoltage-, overcurrent- and overtemperature-protection functions.

Features:

- USB-C PD 3.0 port delivering up to 18 W to charge a handheld game console, tablet or other compatible device
- Overload, overcurrent and overheat protection
- Compact, portable and stylish design for easy travel
- Three-year warranty

Specifications:

Standards and Certifications

- USB 2.0
- PD 3.0

- CE
- RoHS
- WEEE

Ports

- One USB-C with Power Delivery (PD 3.0)

General

- Europlug AC input: 100 – 240 V; 50 – 60 Hz
- USB-C output: 5 – 12 V; maximum 3 A; 18 W
- Voltage/current settings (maximum):
 - USB-C:
 - 5 V / 3 A
 - 9 V / 2 A
 - 12 V / 1.5A

Input Characteristics

- AC rated voltage: 100 – 240 V
- Frequency range: 50 – 60 Hz (± 1 Hz)
- Current: ? 1 A at 100 VAC 60 HZ

Output Characteristics

- Rated voltage: 5 / 9 / 12 V
- Current: 3 A maximum (at constant voltage mode)
- Rated power: 18 watts maximum
- Overshoot voltage: ? 5%

Protection Characteristics

- Short circuit (SCP) with auto-recovery mode
- Overvoltage (OVP) with auto-recovery mode
- Overcurrent (OCP) — current limit: 150% (max)
- Over-temperature (OTP)

Physical

- Dimensions: 6 x 3.9 x 2.2 cm (2.58 x 2.58 x 1.5 in)
- Weight: 0.04 kg (1.41 oz.)
- Housing: plastic

Operating Environment

- Operation Temperature: 0 – 30°C (32 – 86°F)
- Storage Temperature: -20 – 65°C (-4 – 149°F)
- Humidity (noncondensing): 10 – 90%

Package Contents

- Power Delivery Wall Charger - 18 W
- Quick Instruction Guide

