


# KNX interfaces



Computer interface




Dry contacts interface



Logic functions



Programming through ETS





**KNX Universal interface**

**1K.02 - 2 input – 2 LEDs**

**1K.04 - 4 input – 4 LEDs**

- Available with 2 or 4 inputs
- 8 advanced logic functions
- Compact size
- Status LED managing



Includes 2 digital inputs for dry contacts and 2 outputs for LEDs.  
 Device 1K.04.9030 includes 4 digital inputs for dry contacts and 4 outputs for LEDs.  
 These devices (only 34 x 34 x 11 mm) can also be used in installations where the inwall space available is reduced.  
 The digital inputs can interface sensors, traditional buttons, etc.  
 The low voltage output channels can drive LEDs for synoptic panels or switches

For outline drawing see page 6

**Supply specification**

Type of BUS		KNX
Supply voltage	V DC	30
<b>Technical data</b>		
Logic functions		AND, OR, NOT, XOR, NOR, NAND, XNOR, Byte to bit and bit to byte conversions, 1, 2 and 4 bytes threshold
Software compatibility		ETS 5 (or above)
Ambient temperature range	°C	-5...+45
Protection category		IP 40
<b>Approvals</b> (according to type)		—

**KNX USB interface****1K.UB - USB interface for KNX BUS**

- Standard KNX TP backbone
- USB type-B connector
- Compact size, one module wide
- LED indicating BUS status



The modular USB Finder interface has 1 module DIN BAR-mounting size.

Thanks to it you can connect the PC through the USB port in order to manage your KNX system through the ETS software taking up the least possible space.


For outline drawing see page 6

**Supply specification**

Type of BUS		KNX
Supply voltage	V DC	30
<b>Technical data</b>		
Software compatibility		ETS 3 (or above)
Ambient temperature range	°C	-5...+45
Protection category		IP 40
<b>Approvals</b> (according to type)		—


### Ordering information

Example: 1K Series, KNX universal interfaces with 2 IN / 2 OUT, in-wall mounting.




### Wiring diagram

**Type 1K.02**





**Type 1K.04**



### Wired cable

**Type 1K.02 and 1K.04**



**Wired cable for 1K.02.9030**


1.	BLACK	COM
2.	WHITE	INPUT 1
3.	YELLOW	OUTPUT 1
4.	BLACK	COM
5.	NOT CONNECTED	
6.	NOT CONNECTED	
7.	BLACK	COM
8.	GREEN	INPUT 3
9.	BLUE	OUTPUT 3
10.	BLACK	COM
11.	NOT CONNECTED	
12.	NOT CONNECTED	

**Wired cable for 1K.04.9030**

1.	BLACK	COM
2.	WHITE	INPUT 1
3.	YELLOW	OUTPUT 1
4.	BLACK	COM
5.	RED	INPUT 2
6.	ORANGE	OUTPUT 2
7.	BLACK	COM
8.	GREEN	INPUT 3
9.	BLUE	OUTPUT 3
10.	BLACK	COM
11.	VIOLET	INPUT 4
12.	GRAY	OUTPUT 4

## Outline drawings

Types 1K.02 / 04



Type 1K.UB

