



**Miniature circuit breaker (MCB), 2 A, 1p, characteristic: C, DC**

**Part no.** FAZ-C2/1-DC  
**Catalog No.** 279122  
**Alternate Catalog No.** FAZ-C2/1-DC  
**EL-Nummer (Norway)** 0001690999

Similar to illustration

**Delivery program**

Basic function			Miniature circuit-breakers
Number of poles			1 pole
Tripping characteristic			C
Application			Switchgear for DC applications
Rated current	$I_n$	A	2
Rated switching capacity acc. to IEC/EN 60947-2	$I_{cu}$	kA	10
Product range			FAZ-DC

**Technical data**

**Electrical**

Standards			EN 45545-2; IEC 61373
Rated operational voltage	$U_e$	V	
		V DC	250 (per pole)
Rated switching capacity acc. to IEC/EN 60947-2	$I_{cu}$	kA	10
Characteristic			C
Max. back-up fuse		A gL/gG	100
Selectivity Class			3
lifespan			
Lifespan	Operations		> 10000
Direction of incoming supply			Polarity dependent

**Mechanical**

Standard front dimension		mm	45
Enclosure height		mm	80
Mounting width per pole		mm	17.5
Mounting			IEC/EN 60715 top-hat rail
Degree of Protection			IP20, IP40 (when fitted)
Terminals top and bottom			Twin-purpose terminals
Terminal protection			Finger and back-of-hand proof to BGV A2
Terminal capacities		mm <sup>2</sup>	
		mm <sup>2</sup>	1 x 25
		mm <sup>2</sup>	2 x 10
Thickness of busbar material		mm	0.8 ... 2
Mounting position			As required

**Design verification as per IEC/EN 61439**

Technical data for design verification			
Rated operational current for specified heat dissipation	$I_n$	A	2
Heat dissipation per pole, current-dependent	$P_{vid}$	W	0
Equipment heat dissipation, current-dependent	$P_{vid}$	W	1.4
Static heat dissipation, non-current-dependent	$P_{vs}$	W	0
Heat dissipation capacity	$P_{diss}$	W	0

Operating ambient temperature min.	°C	-40
Operating ambient temperature max.	°C	75
linear, per +1 °C, results in a 0.5% reduction of current carrying capacity		

## Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Miniature circuit breaker (MCB) (EC000042)

Electric engineering, automation, process control engineering / Electrical installation, device / Miniature circuit breaker system (MCB) / Miniature circuit breaker (MCB)  
(ecl@ss10.0.1-27-14-19-01 [AAB905014])

Release characteristic		C
Number of poles (total)		1
Number of protected poles		1
Rated current	A	2
Rated voltage	V	250
Rated insulation voltage $U_i$	V	440
Rated impulse withstand voltage $U_{imp}$	kV	4
Rated short-circuit breaking capacity $I_{cn}$ EN 60898 at 230 V	kA	0
Rated short-circuit breaking capacity $I_{cn}$ EN 60898 at 400 V	kA	0
Rated short-circuit breaking capacity $I_{cu}$ IEC 60947-2 at 230 V	kA	10
Rated short-circuit breaking capacity $I_{cu}$ IEC 60947-2 at 400 V	kA	10
Voltage type		DC
Frequency	Hz	50 - 60
Current limiting class		3
Suitable for flush-mounted installation		No
Concurrently switching N-neutral		No
Over voltage category		3
Pollution degree		2
Additional equipment possible		Yes
Width in number of modular spacings		1
Built-in depth	mm	70.5
Degree of protection (IP)		IP20
Ambient temperature during operating	°C	-25 - 75
Connectable conductor cross section multi-wired	mm <sup>2</sup>	1 - 25
Connectable conductor cross section solid-core	mm <sup>2</sup>	1 - 25

## Dimensions

