







Remote operator, 208-240VAC, for size 3

Part no.	NZM3-XR208-240AC
Catalog No.	259850
EL-Nummer (Norway)	0004358803

Similar to illustration

Delivery program

Product range		Accessories	
Accessories		Remote operator, can be synchronized	
Rated operating frequency		AC 50/60 Hz	
Standard/Approval		UL/CSA, IEC	
Construction size		NZM3	
Description		For remote switching of circuit-breakers and switch-disconnectors. ON and OFF switching and resetting by means of two-wire or three-wire control. Local switching by hand possible. Lockable in the 0 position of the remote operator with up to 3 padlocks (hasp thickness: 4 – 8 mm)	
		Can be synchronized	
		Three-wire control	<p>Please note during engineering: Terminal 70/71: NZM-XR: Contact loading according to technical data NZM2-XRD: Full current flows through the contact during make and break! RMQ series contact elements can be used for the NZM2(3.4)-XR(D)...remote operators.</p>
			
		Two-wire control	<p>Terminal 75: NZM-XR: Operational readiness signal when cover closed and not locked. NZM2-XRD: Operational readiness signal when sliding switch set to Auto. Sliding switch with three positions: Manual/Auto/Locked for reliable differentiation of connected positions. AC-15: 400 V; 2 A DC-13: 220 V; 0.2 A</p>
			
		Three-wire control with automatic reset to the 0 position after the switch has tripped	
		Switching cycle:	
			<p>The time interval between OFF and ON is 3 seconds. On commands received during the time interval are ignored within the first 3 seconds after switch off.</p>
		Parallel remote operator connection	
Closing delay	ms	80	
Break time	ms	1000	
Rated control voltage	U _s	V	208 - 240 V 50/60 Hz

Number of poles		3/4 pole
For use with		NZM3(-4) N(S)3(-4)
Project planning information		Cannot be combined with switch-disconnector PN... M22-CK11(20/02) dual auxiliary switch cannot be combined with NZM3-XR... remote operator
Engineering information (sheet catalog)		2/3-wire control and circuit diagrams

Technical data

Remote operator

Rated control voltage	U_s	V	
AC	U_s	V AC	208 - 240
Operating range			
AC		$x U_s$	0.85 - 1.1
DC		$x U_s$	0.85 - 1.1
Motor rating			
AC			
110 V ... 130 V AC	S	VA	350
Minimum signal duration			
with switch on		ms	30
with switch off		ms	250
Lifespan, mechanical	Operations		15000
Maximum operating frequency		Ops./h	
Max. operating frequency		Ops/h	60
Terminal capacities		mm ²	
Solid or flexible conductor, with ferrule		mm ²	0,75 - 2,5
		AWG	18 ... 14

Design verification as per IEC/EN 61439

IEC/EN 61439 design verification		
10.2 Strength of materials and parts		
10.2.2 Corrosion resistance		Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures		Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat		Meets the product standard's requirements.
10.2.3.3 Verification of resistance of insulating materials to abnormal heat and fire due to internal electric effects		Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation		Meets the product standard's requirements.
10.2.5 Lifting		Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact		Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions		Meets the product standard's requirements.
10.3 Degree of protection of ASSEMBLIES		Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances		Meets the product standard's requirements.
10.5 Protection against electric shock		Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components		Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections		Is the panel builder's responsibility.
10.8 Connections for external conductors		Is the panel builder's responsibility.
10.9 Insulation properties		
10.9.2 Power-frequency electric strength		Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage		Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material		Is the panel builder's responsibility.
10.10 Temperature rise		The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function		The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Technical data ETIM 7.0

Low-voltage industrial components (EG000017) / Motor operator for power circuit-breaker (EC001030)

Electric engineering, automation, process control engineering / Low-voltage switch technology / Circuit breaker (LV < 1 kV) / Electrical drive for circuit breakers (ecl@ss10.0.1-27-37-04-12 [AKF010013])

Type of switch drive		Motor drive
Rated control supply voltage Us at AC 50Hz	V	208 - 240
Rated control supply voltage Us at AC 60Hz	V	208 - 240
Rated control supply voltage Us at DC	V	0 - 0
Voltage type for actuating		AC

Approvals

Product Standards	UL489; CSA-C22.2 No. 5-09; IEC60947, CE marking
UL File No.	E140305
UL Category Control No.	DIHS
CSA File No.	022086
CSA Class No.	1437-01
North America Certification	UL listed, CSA certified

Dimensions

