

HANNspree

HANNSpad

HANNspree Pad 10.1" Apollo
P/N: SN1ATP4B
10.1" IPS Dual-Band Wi-Fi



10.1" / 25,65 cm

Part. No.: SN1ATP4B

SIZE, RESOLUTION

10.1" 10.1" IPS Panel
25,65 cm

1280 x 800 1280 x 800

CPU, RAM MEMORY

x4 Quad Core QuadCore CPU
64 bit, 2GHz

3 GB RAM 3 GB DDR

CAMERA, STORAGE

Dual Camera Dual Camera
5MP AF / 2MP

32 GB STORAGE 32 GB

Wi-Fi, CONNECTIVITY

2.4 GHz 5.0 GHz Dual Band 2.4 + 5 GHz
WLAN 802.11 a/b/g/n+ac

USB Type C Micro-HDMI Type-C USB 2.0
Micro-HDMI

[Technical Specifications >>>](#)

Name / Part Nr.	HANNspree Pad 10.1" Apollo / P/N SN1ATP4B
Screen Size	25.65 cm / 10.1 Inch
Resolution (H x V)	1280 x 800, 16:10 Aspect Ratio, Brightness: 250 cd/m ²
Viewing Angle	170° (V) / 170° (H)
Touchscreen Type	Multi Point Capacitive Touch Panel; Type: P + G TP Thickness: 1.65 mm
CPU	Quad Core CPU MT8168 Cortex ARM A53 64 bit, up to 2.0 GHz
GPU	Mali G52, up to 800Mhz
Memory	3GB RAM eMCP
Storage Internal	32GB eMCP
Storage External	Micro-SD/Micro-SDHC Card, max. 128GB
WLAN	Wi-Fi IEEE 802.11 a/b/g/n+ac 2.4/5GHz
Bluetooth	5.0
Camera	Front 2MP / Rear 5MP with AF
Microphone	Built-in
Speakers	Built-in, Stereo Speakers 2 x 1W
Headphone Output	3.5mm Earphone jack
HDMI	Micro HDMI (V. 1.4 D TYPE)
Type-C USB 2.0	Yes
GPS / G-Sensor	Yes / Yes (4 Directions)
3 Axis Accelerometer	Yes
OTG	Yes
Battery Type	Li-Ion Battery 5.000 mAh, 3.7 Volt
Battery Life	>4 hours (1080p Video playback, Wi-Fi Off, Brightness 60%, Webcam off)
Power Adaptor	AC Adaptor: 5V, 2A

Operating Temperature	5 ~ 40° Celsius
Operating Humidity	10 ~ 85%
Case Material	Plastic with oil-rubber painting
Product Dimensions	243.6 x 172.2 x 9.9 (W x H x D mm)
Packaging Dimensions	280 x 200 x 50 (W x H x D mm)
Net Weight	880Grams
Gross Weight	950 Grams
Control Keys	Power, Volume +/-, Reset
Operating System	Android 10 (Android Q)
UI Language	Android default
Accessory	1 Power Adaptor with EU and UK clips; 1 USB Cable (120 cm); 1 OTG connector; Quick Start Guide; Warranty Card
Packaging	Color retail box
EAN Code	4711404023217

PART. NO.:
SN1ATP4B

