




RoHS Compliant



Wire sticker(REV.3)

- Electrical Test:
- 1.100% TEST OPEN SHORT MIS-WIRE.
 - 2.CONTACT RESISTANCE:3Ω MAX.
 - 3.INSULATION RESISTANCE:5MΩ MIN.
 - 4.HI-POT:300V DC/10MS.
 - 5.Support PD 20V 3A.
 - 6.Support USB 3.2 Gen2 10Gbps
 - 7.Real Test Passed 3840*2160P 30Hz.
 - 8.Real Test Not Twinkling,Double Vision and Decolor.

Pin Assignment



D		
C	更改總長為1200mm-SR-SR	2024-07-03
B	更新彩盒版本为V2/線上貼 (REV. 3)	2024-04-07
VER.A	REVISE	DATE

Company: CONRAD

C	1	Z-2316532	45P PVC BLACK		G
B			TYPE CM Solder Type (Black Insulator,Nickel plated)+C 10nF	2	PCS
A			UL2725(32#*1P+DAM)*4C+32#*1P+32#*4C+22#*1C+AB,OD=4.8mm,BLACK PVC JACKET.	1	PCS
NUMBER	BOM.NO		PRODUCT SPECIFICATIONS	Quantity	Unit

Item	2316532	
Draw	Kobe	Date: 2020.08.20
Approval		
Duty	F16	BOM.NO: 14041


RoHS Compliant

CONRAD
GERMANY
BEST NO.: 2316532
PCS.: 100 PCS
MODEL NO.: U3.2-CML-CML-1.2M
ORDER NO.:
WEIGHT(KG.): KGS


外箱側麥

CONRAD
HAMBURG
C/NO.:
MADE IN CHINA


外箱正麥



產品直接裝入VP1-20款彩盒內(105*140*20mm)



100PCS/CTN (580*230*230mm) 一排50pcs 上下兩排



D		
C		
B		
VER.A	REVISE	DATE

Company: CONRAD

Item	2316532	
Draw	Kobe	Date: 2020.08.20
Approval		
Duty	F16	BOM.NO:14041