



Discover more details and matching accessories online!

Robust counting scale with large article memory, convenient operating philosophy and checkweighing display, counting resolution up to 30,000 points

Features

- Innovative counting with tolerance range (Checkweighing): The counting process can be supported visually and/or audibly and this therefore makes portion division, dispensing and grading easier
 - visual signal: the colour of the display changes depending on the counting result (not enough/ ok/too much)
 - audible signal: the frequency of the audible signal changes depending on the counting result (not enough/ok/too much)
- Ideal for workshops for people with disabilities, particularly loud or quiet environments, where operators change frequently, etc.
- Three displays for weight display, reference weight, total pieces
- The automatic reference weight optimisation of reference weight gradually improves the average piece weight value
- Programmable using numerical key pad:
 - required reference quantity
 - known reference weight

- Counting results memory: adds up all individual piece counts, result is shown in total weight and total pieces
- PRE-TARE function for manual subtraction of a known container weight, useful for checking fill-levels
- 20 direct price keys for frequently recurring reference weights and PRE-Tare values
- Memory for 50 reference weights and PRE-Tare values
- Thanks to rechargeable battery operation, compact, lightweight construction, it is suitable for the use in several locations
- Changes from counting mode to weighing mode at the touch of a key
- Energy management: Backlight turns off after 5 sec, can be switched off
- Protective working cover included with delivery

Technical data

- Large backlit LCD displays, digit height 18 mm
- Dimensions weighing surface, stainless steel, W×D 315×215 mm
- Overall dimensions W×D×H 350×330×120 mm
- Rechargeable battery pack integrated, as standard, operating time up to 160 h without backlight, charging time approx. 14 h
- Net weight approx. 4,0 kg
- Permissible ambient temperature -10 °C/40 °C

STANDARD



OPTION



Model	Weighing capacity	Readability	Smallest part weight (Normal)	Counting resolution	Options
					Calibr. Certificate
	[Max] kg	[d] g	g/piece	Points	DAkKS accr. KERN
KERN					
CIB 3K-4	3	0,2	1	30.000	963-127
CIB 6K-4	6	0,5	2	30.000	963-128
CIB 10K-3	15	1	5	30.000	963-128
CIB 30K-3	30	2	10	30.000	963-128